

CERTIFICATE

KEMA No.: 2121597.02

Issued to:
Applicant:

Hans Wagner GmbH
Brunnenstrasse 2
96358, REICHENBACH/OFR, Germany

Manufacturer/Licensee:

Hans Wagner GmbH
Brunnenstrasse 2
96358, REICHENBACH/OFR, Germany

Product(s) : appliance connectors; (2-pole)
Trade name(s) : HAWA
Type(s)/model(s) : D1



The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

KEMA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard EN 60320-1:2001 + A1: 2007
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 2121597

KEMA hereby grants the right to use the ENEC KEMA-KEUR certification mark.

The ENEC KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration of the ENEC KEMA-KEUR certification agreement and under the conditions of the ENEC KEMA-KEUR certification agreement.

This certificate is issued on: 21 January 2009 and expires upon withdrawal of one of the above mentioned standards.

KEMA Quality B.V.

drs. G.J. Zoetbrood
Managing Director

H.L. Schendstok
Certification Manager

ACCREDITED BY
THE DUTCH COUNCIL
FOR ACCREDITATION



© Integral publication of this certificate is allowed

SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

product	: appliance connectors; (2-pole)
trade name	: HAWA
type	: D1
rated current	: 10 A
rated voltage	: 250 V~
standard sheet	: C13
temperature limit	: T70
earthing	: with earthing contact
design	: non-rewirable
applied flexible cord	: H05VV-F 3G0,75, 3G1,0 and 3G1,5 mm ²
certification mark	: HAR certified
cord termination	: crimped connection
description	: body of thermoplastic material as part of an incomplete cord set for class I appliances
markings	: are shown on the body

TESTS**Test requirements**

EN 60320-1:2001 + A1:2007

Test result

The test results are laid down in KEMA test file 2121597.02.

Conclusion

The examination proved that all test requirements were met.

Tested by : H.R.M. Barends

Checked by : T.J. Overklift Vaupel Kleyn

**Factory locations**Hans Wagner GmbH,
Birkenstrasse 14, 96358, REICHENBACH/OFR, Germany



ZEICHENGENEHMIGUNG
MARKS LICENCE

Aktenzeichen:
File ref.:
998500-1560-0002 / 66192

Ausweis-Nr.:
Licence No.:
40015003

Datum
Date
2006-02-14

Stecker 2-polig mit Schutzkontakt
Plug 2-pole with earthing contact

Ausführung: abgewinkelte Leitungseinführung
Construction: angled cable entry

Anlage-Nr.: 400A
Appendix No.:

Position im VDE-Ausweis Position in VDE-licence	Typ(en) Type(s)	Leitungsaufdruck Marking on cable		
B1	Kordes Kabel			
B1	EUROELECTRIC GROUPE PIRELLI 0286			
			(max. 2 m)	
		H03VV-F 3G 0,5 mm ²	--	--
		H03VV-F 3G 0,75 mm ²	X	--
		H05VV-F 3G 0,75 mm ²	X	--
		H05VV-F 3G 1,0 mm ²	X	--
		H05VV-F 3G 1,5 mm ²	X	--
		H05RR-F 3G 0,75 mm ²	X	--
		H05RR-F 3G 1,0 mm ²	--	--
		H05RR-F 3G 1,5 mm ²	X	--
		H05RN-F 3G 0,75 mm ²	--	--
		H05RN-F 3G 1,0 mm ²	X	--
		H07RN-F 3G 1,0 mm ²	--	--
		H07RN-F 3G 1,5 mm ²	--	--
		H03RT-H 3G 0,75 mm ²	--	--
		H03RT-H 3G 1,0 mm ²	--	--
		H05V2V2-F 3G 0,75 mm ²	--	--
		H05V2V2-F 3G 1,0 mm ²	--	--
			--	--
			--	--
			--	--
			--	--
			--	--
			--	--
			--	--
			--	--
			--	--
			--	--
			--	--

X Δ genehmigte Ausführung / approved version

-- Δ nicht genehmigt / not approved

Werkstoff der Trägereile: Typ und Hersteller
Material of the base: Type and manufacturer

geprüft unter Az.: / approved under
VDE-Ref.: 15181-1560-0006

Inneneinsatz: Typ und Hersteller
Insert: Type and manufacturer

B04...
Taller GmbH

VDE Prüf- und Zertifizierungsinstitut

Diese Anlage gilt nur in Verbindung mit Blatt 1 der Zeichengenehmigung
This Appendix is only valid in conjunction with page 1 of the marks licence

VDE Prüf- und Zertifizierungsinstitut
VDE Testing and Certification Institute
i. A. M.



Fachgebiet FG33
Section FG33
VDE