

EG-Konformitätserklärung



Name/Anschrift des Ausstellers: Georg Schlegel GmbH & Co. KG
Kapellenweg 4
88525 Dürmentingen

Dokumentations-Bevollmächtigter: T.Gairing, Georg Schlegel GmbH & Co. KG
Kapellenweg 4
88525 Dürmentingen

Produktbezeichnung: Not-Halt / Not-Aus Befehlsgeräte

Die bezeichneten Produkte erfüllen die Bestimmungen der Richtlinien:

| Produkt / Typenbezeichnungen | Richtlinie und angewandte Normen | | | | | | | | | |
|---|----------------------------------|-----------------|---------------------------|---------------------------|------------------------------|---------------------------|-------------------|-------------------------|-------------------------------|------------------|
| | Nsp | | | Masch | | | EMV | | | |
| | 2006/95/EG vom 12.12.2006 | EN 61058-1:2008 | EN 60947-5-1:2004/A1:2009 | EN 60947-5-5:1997+A1:2005 | 2006/42/EG vom 17.05.2006 | EN 60947-5-5:1997+A1:2005 | EN ISO 13850:2008 | EN 60204-1:2006/A1:2009 | 2004/108/EG vom 12.12.2006 | EN 62026-2: 2013 |
| OKJ(B)UV, RKUV28, OKUVGB, RK(U)VGB, RKUV40_496, RKUV40, RKUV32, RXJ(B)UV, RX(B)(SK)(L)UV(SE)(P), QXJ(B)UV, QR(B)(J)(SK)(L)UV(SE)(P)(70), FRUV(L), RRJUV, FRVK(P)(AL)(L)(O)(OO)(OI)(OOI)(OII)(OOO)(P)(L)AU, XFV32, RUV, KR(G)V, RV, QRV, KR(J)(B)UV(70), DXRV(G)(S)40(S) (SS)(S3); DXRV39(MRT) (GRT)(SRT)(PF), DXRV52(M)(G)(S)RT | • | | • | • | • | • | • | • | | |
| AZOSOI(L)AU, AZSOSO(L)AU, BZ(L)O(5)(K)(L)AU, AT(L)AU, AZ011(L)AU, AZ00(L)AU, AZ(L)2(L)AU, AZOSOI(L)AU, AZSOSO(L)AU, AZ2N(L)AU, AZ(L)4O(L)AU, BZ(L)OO(5)(K)(L)AU, BZ(L)OI(5)(K)(L)AU, BZ(L)OS(5)(K)(L)AU, BZ(L)O(5)(K)(L)AU, DST(O)(OSDE)(I), DMSTOSF,DT(O)(I), DMTOSF(A), DMR, DSAL | • | • | • | | • | • | • | • | | |
| MT(O)(I)(SF)(SFE)(ON)(IV)(97)(Z)(L)545, MHT(O)(OO)(IOO)(OSF)(OSFO)(OSFI)(OSFOI)(OSFOIL)(L)545 (OSFE)(OSFEO)(OSFEOO)(OSFEOI), MZ(TI)(TO), MAL, MHR_3, MHR_5, MTZU(L)564, ETR, PTOO(L)AU, PTPOO(L)AU, PTPOI(L)AU, PTFOO(L)AU, PTFOI(L)AU, PTFPOI(L)AU, PTFPOO(L)AU, PTS(L)(OOO)(OOI)(OO)(OI)(L)AU, PTSFP(L)(OOO)(OOI)(OO)(OI)(L)AU, FRT(F)(P)(L)(OOI)(OO)(OI)(30)(S)(L)AU | | | | | • | • | • | • | • | • |
| ASI_SAW(16)(22)(A)(E) | | | | | • | • | • | • | • | • |
| SILH_ASI(E)(A)_QR(B)(SK)(L)UV(SE)(P) | • | | • | • | • | • | • | • | • | • |
| SIL_QR(B)(SK)(L)UV(SE)(P)(O)(OI)(OO)(OOI)(OSF)(L)M12, MB(M)(P)(W)(124)(125)(128)FRVK(L)(OO)(OOI)(OOO)(L)AU (NOOITI) (NOOM)(NOOTLI) (NOOOTI) (NOITI) (NOII) (NOOTI) (NLOOTI) (NOOOM) (NLOITI) (NLOIM) (NOOIM) | • | | • | • | • | • | • | • | | |
| SIL(H)(16)(22)/1, MB(M)(P)(W)(124)(125)(128)(GB)(GB2)_LEER | • | • | | | • | | | • | | |
| RSK22, RRSK, RSKF22, RSKS | | | | | • | • | • | | | |

Dürmentingen, 23.04.2014

(Ort, Datum)

(Rechtsverbindliche Unterschrift des Ausstellers)

EC Declaration of Conformity



Manufacturer's name and address:

Georg Schlegel GmbH & Co. KG
Kapellenweg 4
88525 Dürmentingen

Authorized person for documentation:

T.Gairing, Georg Schlegel GmbH & Co. KG
Kapellenweg 4
88525 Dürmentingen

Product:

Emergency-Stop Control Units

The designated products are in conformity with the European Directives:

| Product /Type designation | European Directives and used standards | | | | | | | | | |
|---|--|-----------------|---------------------------|---------------------------|------------------------------|---------------------------|-------------------|-------------------------|-------------------------------|------------------|
| | Nsp | | | Masch | | | EMV | | | |
| | 2006/95/EC vom 12.12.2006 | EN 61058-1:2008 | EN 60947-5-1:2004/A1:2009 | EN 60947-5-5:1997+A1:2005 | 2006/42/EC vom 17.05.2006 | EN 60947-5-5:1997+A1:2005 | EN ISO 13850:2008 | EN 60204-1:2006/A1:2009 | 2004/108/EC vom 12.12.2006 | EN 62026-2: 2013 |
| OKJ(B)UV, RKUV28, OKUVGB, RK(U)VGB, RKUV40_496, RKUV40, RKUV32, RXJ(B)UV, RX(B)(SK)(L)UV(SE)(P), QXJ(B)UV, QR(B)(J)(SK)(L)UV(SE)(P)(70), FRUV(L), RRJUV, FRVK(P)(AL)(L)(O)(OO)(OI)(OOI)(OOO)(OII)(P)(L)AU, XFV32, RUV, KR(G)V, RV, QRV, KR(J)(B)UV(70), DXRV(G)(S)40(S) (SS)(S3); DXRV39(MRT) (GRT)(SRT)(PF), DXRV52(M)(G)(S)RT | • | | • | • | • | • | • | • | | |
| AZOSOI(L)AU, AZSOSO(L)AU, BZ(L)O(5)(K)(L)AU, AT(L)AU, AZO11(L)AU, AZO0(L)AU, AZ(L)2(L)AU, AZOSOI(L)AU, AZSOSO(L)AU, AZ2N(L)AU, AZ(L)4O(L)AU, BZ(L)OO(5)(K)(L)AU, BZ(L)OI(5)(K)(L)AU, BZ(L)OS(5)(K)(L)AU, BZ(L)O(5)(K)(L)AU, DST(O)(OSDE)(I), DMSTOSF,DT(O)(I), DMTOSF(A), DMR, DSAL | • | • | • | | • | • | • | • | | |
| MT(O)(I)(SF)(SFE)(ON)(IV)(97)(Z)(L)545 MHT(O)(OO)(IOO)(OSF)(OSFO)(OSFI)(OSFOI)(OSFOIL)(L)545 (OSFE)(OSFEO)(OSFEOO)(OSFEOI) MZ(TI)(TO), MAL, MHR_3, MHR_5,MTZU(L)564 ETR, PTOO(L)AU, PTPOO(L)AU, PTPOI(L)AU, PTFOO(L)AU, PTFOI(L)AU, PTFPOI(L)AU, PTFPOO(L)AU, PTS(L)(OOO)(OOI)(OO)(OI)(L)AU, PTSFP(L)(OOO)(OOI)(OO)(OI)(L)AU, FRT(F)(P)(L)(OOI)(OO)(OI)(3O)(S)(L)AU | | | | | | | | | | |
| ASI_SAW(16)(22)(A)(E) | | | | | • | • | • | • | • | • |
| SILH_ASI(E)(A)_QR(B)(SK)(L)UV(SE)(P) | • | | • | • | • | • | • | • | • | • |
| SIL_QR(B)(SK)(L)(U)V(SE)(P)(O)(OI)(OO)(OOI)(OSF)(L)M12, MB(M)(P)(W)(124)(125)(128)FRVK(L)(OO)(OOI)(OOO)(L)AU (NOOITI) (NOOM)(NOOTLI) (NOOOTI) (NOITI) (NOIIL) (NOOTI) (NLOOTI) (NOOOM) (NLOITI) (NLOIM) (NOOIM) | • | | • | • | • | • | • | • | | |
| SIL(H)(16)(22)/1, MB(M)(P)(W)(124)(125)(128)(GB)(GB2)_LEER | • | • | | | • | | | • | | |
| RSK22, RRSK, RSKF22, RSKS | | | | | • | • | • | | | |

Dürmentingen, 23.04.2014

(Place, date)

(Legally binding signature of the issuer)