


Adapter Sub-D 25 Pin Buchse > Terminalblock 27 Pin

Kurzbeschreibung

Dieser Sub-D zu Terminalblock Adapter ist für spezielle Industrieanwendungen geeignet, wie z.B. zum Anschluss einzelner Kabelstränge mit offenen Kabelenden. Anwendung findet der Adapter beispielsweise im Hobbybereich, wie Eisenbahnmodellbau.



Art.	65317
EAN	4043619653171
Ursprungsland	China
Zolltarifnummer	84718000

Abbildungen

Technische Daten

- Sub-D 25 Pin Buchse
- 3 x 9 Pin Terminalblock (25 Pins beschaltet)
- Pitch 3.81 mm
- Buchse mit Muttern
- Maße (LxBxH): 54,2 mm x 53,04 mm x 16,05 mm

Packungsinhalt

- Adapter

Verpackung


- Delock Poly Bag

Adapter Sub-D 25 pin female > Terminal Block 27 pin

Description

This Sub-D to terminal block adapter is made for special industrial application e.g. for connecting single wires with open cable heads. It also can be used in the hobby area for example for model railroading.

Images



Ref.	65317
EAN	4043619653171
Country of origin	China
Customs tariff number	84718000

Specification

- Sub-D 25 pin female
- 3 x 9 pin terminal block (25 pins connected)
- Pitch 3.81 mm
- Female port with screw nuts
- Dimension (LxWxH): 54.2 mm x 53.04 mm x 16.05 mm

Package content




- Adapter

Package

- Delock poly bag



WIRING TABLE	
DB25 PIN #	TERMINAL PIN #
1	1
2	2
3	3
4	4
5	5
6	6
.....
.....
.....
20	20
21	21
22	22
23	23
24	24
25	25
SHELL	SHL

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/11/11	Liu Jian Ping



JACKSCREW DETAIL

2X #4-40 JACKSCREW



EVA T=4mm

Part name:
Adapter terminal block > Sub-D 25 pin female

Electrical Character:

- 1> 100% open&short testing
- 2> With understanding voltage:DC 500 V 0.01 Sec.
- 3> Insulation Resistance: 50M Ohm (Min)
- 4> Conductive Resistance: 2 Ohm(Max)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN mm	APPROVALS	DATE
	DRAWN BY May	7/11/2011
DIMENSIONAL TOLERANCES: .X = ±0.3 .XX = ±0.2 .XXX = ±0.1	CHECKED BY Gang	7/11/2011
	APPROVED BY Steven	7/12/2010
ANGULAR TOLERANCES: ALL = ± 1°	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	
PROJECTION	COLOR VARIATIONS MAY OCCUR	



Item no. 65317

Barcode: 4043619653171

File: 88072