

UL-No. E235797

Werkstoff:
 E-CU sn = Elektrolytkupfer verzinkt


















Matière:
 E-CU sn = cuivre électrolytique étamé

Material:
 E-CU sn = tin-plated electrolytic copper

Temperaturbeständigkeit:
 -55°C bis +105°C

Résistant à une température de:
 -55°C à +105°C

Temperature range:
 -55°C up to +105°C

PA														
mm ²	AWG	für Bolzen pour borne for stud mm	Farbe Couleur Colour	Artikelnummer Numéro d'article Part-No.	DIN	øD mm	øD1 mm	øD3 mm	øD4 mm	L mm	A mm	R mm	S mm	Werkzeuge Outils Toolings
0.14-0.5	26-22	M3		3596c	*	3.2	1	5	2.3	12	4	5	0.5	3974n, 3984l, 3984lx
0.5-1	22-18	M3		3604c	*	3.2	1.6	6	4	17	5	4.5	0.8	3974n, 3983p.1, 3984c, 3984cx, 3984o, 3984ox, 3986c, 3986n, 3986s
	22-18	M3.5		3608c	*	3.7	1.6	6	4	17	5	4.5	0.8	
	22-18	M4		3612c	*	4.3	1.6	6.8	4	18	5	4.5	0.8	
	22-18	M4		3614c	*	4.3	1.6	8	4	18	5	6	0.8	
	22-18	M5		3616c	*	5.3	1.6	10	4	19	5	6.5	0.8	
	22-18	M6		3619c	*	6.5	1.6	11	4	21	5	10	0.8	
1.5-2.5	16-14	M3		3625c	*	3.2	2.3	5.5	4.5	19	5	4.5	0.8	3984ox, 3986c, 3986n, 3986s
	16-14	M3.5		3629c	*	3.7	2.3	6	4.5	17	5	4.5	0.8	
	16-14	M4		3633c	*	4.3	2.3	6.8	4.5	18.7	5	4.5	0.8	
	16-14	M4		3635c	*	4.3	2.3	8	4.5	18	5	6	0.8	
	16-14	M5		3637c	*	5.3	2.3	10	4.5	20	5	6.5	0.8	
	16-14	M6		3639c	*	6.5	2.3	11	4.5	22	5	7.5	0.8	
4-6	12-10	M4		3652c	*	4.3	3.6	8	6.4	21	6	6	1	3974n, 3984o, 3986c, 3986n, 3986s
	12-10	M5		3656c	*	5.3	3.6	10	6.4	22	6	6.5	1	
	12-10	M6		3660c	*	6.5	3.6	11	6.4	23	6	7.5	1	
	12-10	M8		3664c	*	8.5	3.6	14	6.4	26	6	10	1	