



Extra scharfe Schneiden

Äußerst präzise Schneideigenschaften dank der messerartig geschliffenen Vorschneiden

Extra sharp cutting edges

Extremely precise cutting performance thanks to the knife-edge ground pre-cutting edges

Filos especialmente afilados

Excepcionales y precisas propiedades de corte gracias a los filos afilados como un cuchillo

Hitzebeständig

Bohrungen bis 450° sind möglich

Heat resistant

Drilling up to 450° is possible

Termoestable

Posibilidad de perforaciones de hasta 450°

Exakte Bohrungen

Die Doppelfase ermöglicht exakte Führung ohne Durchrutschen

Precise drilling

The double chamfer enables exact guidance without slipping

Perforaciones exactas

La doble fase permite una dirección exacta sin que se deslice



D HSS Maschinen-Holzspiralbohrer

E HSS dowel drills

ES Brocas para madera HSS

Einsatzbereich:

Hitzebeständig bis 450° C. Zum Bohren von Weich- und Harthölzern, Spanplatten, Hartfasersplatten, zum Dübellochbohren.

Range of application:

Heat resistant up to 450° C. For drilling in soft and hard wood, in chipboards, fibreboards, for drilling dowel holes.

Ámbito de aplicación:

Termostable hasta 450 °C. Adecuada para perforar maderas blandas y duras, tablas de madera aglomerada, tableros duros tratados, para perforar agujeros para espigas.




Hitzebeständig
Heat resistant
Termostable



Scharfe Schneiden
Sharp cutting edges
Filos bien afilados



Punktgenaues Anbohren
Highly accurate centering
Perforación de gran precisión



Oberfläche: blank
Surface: bright
Superficie: brillante



Einzelverpackung
Single pack
Embalaje individual

d1 mm	l1 mm	l2 mm	d2 mm	Code 620 Art.-Nr.	Inh. Cont.	
3,00	61	33		0062000300100	1	10
4,00	75	43		0062000400100	1	10
5,00	86	52		0062000500100	1	10
6,00	93	57		0062000600100	1	10
8,00	117	75		0062000800100	1	10
10,00	133	87		0062001000100	1	10
12,00	151	101	9,50	0062001200100	1	10



Holzbohrer
wood drills
brocas para madera