



Your Power Safeguard™
您的电路安全卫士



TECHNICAL PARAMETERS/ 技术参数:

CATALOG NO. 目录编号	CURRENT RATING 额定电流	SAFETY APPROVALS 安全认证								
		CCC			VDE			cRus		
		U5 AC	U6 AC	U0 AC	U5 AC	U6 AC	U0 AC	U5 AC/DC	U6 AC/DC	U0 AC/DC
10aR0.25U5/U6/U0	250mA	●	●	●	●	●	●	●	●	●
10aR0.31U5/U6/U0	3.15mA	●	●	●	●	●	●	●	●	●
10aR0.4U5/U6/U0	400mA	●	●	●	●	●	●	●	●	●
10aR0.44U5/U6/U0	440mA	○	○	○	○	○	○	●	●	●
10aR0.5U5/U6/U0	500mA	●	●	●	●	●	●	●	●	●
10aR0.63U5/U6/U0	630mA	●	●	●	●	●	●	●	●	●
10aR0.8U5/U6/U0	800mA	●	●	●	●	●	●	●	●	●
10aR1U5/U6/U0	1A	●	●	●	●	●	●	●	●	●
10aR1.25U5/U6/U0	1.25A	●	●	●	●	●	●	●	●	●
10aR1.6U5/U6/U0	1.6A	●	●	●	●	●	●	●	●	●
10aR2U5/U6/U0	2A	●	●	●	●	●	●	●	●	●
10aR2.5U5/U6/U0	2.5A	●	●	●	●	●	●	●	●	●
10aR3U5/U6/U0	3A	●	●	●	●	●	●	●	●	●
10aR3.15U5/U6/U0	3.15A	●	●	●	●	●	●	●	●	●
10aR4U5/U6/U0	4A	●	●	●	●	●	●	●	●	●
10aR5U5/U6/U0	5A	●	●	●	●	●	●	●	●	●
10aR6U5/U6/U0	6A	●	●	●	●	●	●	●	●	●
10aR6.3U5/U6/U0	6.3A	●	●	●	●	●	●	●	●	●
10aR7U5/U6/U0	7A	●	●	●	●	●	●	●	●	●
10aR8U5/U6/U0	8A	●	●	●	●	●	●	●	●	●
10aR9U5/U6/U0	9A	●	●	●	●	●	●	●	●	●
10aR10U5/U6/U0	10A	●	●	●	●	●	●	●	●	●
10aR11U5/U6/U0	11A	○	○	○	○	○	○	●	●	●
10aR12U5/U6/U0	12A	●	●	●	●	●	○	●	●	●
10aR12.5U5/U6/U0	12.5A	●	●	●	●	●	○	●	●	●
10aR15U5/U6/U0	15A	●	●	●	●	●	○	●	●	●
10aR16U5/U6/U0	16A	●	●	●	●	●	○	●	●	●
10aR20U5/U6/U0	20A	●	●	●	●	●	○	●	●	○
10aR25U5/U6	25A	●	●	●	●	●	○	●	●	○
10aR30U5/U6	30A	●	●	●	●	●	○	●	●	○
10aR32U5/U6	32A	○	○	○	●	●	○	●	●	○

U5 DENOTES FOR 500V

U5 表示 500V

U6 DENOTES FOR 690V

U6 表示 690V

U0 DENOTES FOR 1000V

U0 表示 1000V

● DENOTES FOR APPROVAL

● 表示已取得安全认证

Recommended fuseblocks/fuseholders for 10.3mmx38mm fuses

See Model of product: HC101A HC101D HF-103D HF-104A

适用于 10.3mmx38mm 熔断体的支持件

详见产品型号: HC101A HC101D HF-103D HF-104A



HC10aR 250mA-32A

Class of Operation: aR

保护特性: aR




Standard/ 标准: IEC 60269-4, GB/T 13539.4, UL 248-13

INTERRUPTING CAPACITY / 分断能力:

120,000 amperes at 500V AC (250mA-30A) CCC
120,000 amperes at 500V AC (250mA-32A) VDE/CURUS
80,000 amperes at 690V AC (250mA-30A) CCC
80,000 amperes at 690V AC (250mA-32A) VDE/CURUS
50,000 amperes at 1000V AC (250mA-30A) CCC
50,000 amperes at 1000V AC (250mA-32A) CURUS
50,000 amperes at 1000V AC (250mA-10A) VDE
120,000 amperes at 500V DC (250mA-32A) CURUS
50,000 amperes at 690V DC (250mA-32A) CURUS
30,000 amperes at 1000V DC (250mA-32A) CURUS

Dimensions/ 尺寸:

Unit 单位: mm



ELECTRICAL CHARACTERISTICS/ 电气特性:

% of CURRENT RATING 额定电流的 %		BLOWING TIME 熔断时间	
		250mA-5A	6A-32A
100%	最快 Min.	4 hours	4 hours
	最慢 Max.	1 seconds	10 seconds
400%	最快 Min.	3 ms	10 ms
	最慢 Max.	20 ms	30 ms
1000%	最快 Min.		
	最慢 Max.		

HC10aR 平均 I-T 曲线图 (仅供参考)

AVERAGE I-T CHARACTERISTICS CURVE
(FOR REFERENCE ONLY)

