

TECHNISCHE DATEN:

Aufbau

Hutmutter	Edelstahl 1.4305
Lamelleneinsatz	Polyamid PA6 V-2
Dichtring	Polychloropren-Nitrilkautschuk CR/NBR
Zwischenstutzen	Edelstahl 1.4305
O-Ring	Nitrilkautschuk NBR
Anschlussgewinde	metrisch, nach EN 60423

Eigenschaften

- integrierte Zugentlastung
- Verdrehenschutz
- großer Dicht- und Klemmbereich
- montagefreundlich

Temperaturbereich -20 °C / +100 °C (dynamisch)
-40 °C (statisch, kurzzeitig)

Schutzart IP68 / IP69K*

Prüfnorm UL 514B

UL / CSA-File E140310

GL T.A. Certificate 44 608 - 07 HH

Hinweis Angaben zu den Prüfungen - siehe Anhang, mit Dichtring und O-Ring aus FKM auf Anfrage

TECHNICAL DATA:

Configuration

Dome nut	Stainless steel 1.4305
Lamellar insert	Polyamide PA6 V-2
Sealing ring	Polychloroprene-Nitrile rubber CR/NBR
Gland body	Stainless steel 1.4305
O-ring	Nitrile rubber NBR
Connecting thread	metric, as per EN 60423

Properties

- integrated anchorage
- protection against twisting
- wide sealing and clamping range
- easy-to-install

Temperature range -20 °C / +100 °C (dynamic)
-40 °C (static, short term)


Protection grade IP68 / IP69K*

Test standard UL 514B

UL / CSA-File E140310

GL T.A. Certificate 44 608 - 07 HH

Comment details about tests - see annex, with sealing ring and O-ring made of FKM on request




Merkmale

Characteristics

Anschlussgewinde Standardlänge

Connecting thread standard length

A	ØC mm	$\frac{H}{mm}$ L mm	SW1 mm	SW2 mm	H mm		Art.-Nr. / Part No.
M12x1,5	3 - 6	5	14	14	25	50	50.612 ES
M16x1,5	5 - 9	5	17	17	30	50	50.616 ES
M20x1,5	9 - 13	6	22	22	33,5	50	50.620 ES
M25x1,5	11 - 16	7	27	27	36,5	50	50.625 ES
M32x1,5	14 - 21	8	34	34	38	25	50.632 ES
M40x1,5	19 - 27	8	43	43	41	10	50.640 ES
M50x1,5	24 - 35	9	55	55	49,5	5	50.650 ES
M63x1,5	32 - 42	10	65	65	52,5	5	50.663 ES

*IP69K geprüft für M12 - M25, M50, M63

*IP69K tested for M12 - M25, M50, M63