

Datasheet

Item no. TC-DS311SW



1. Rating:AC 125V 3A
2. ContactR:50mΩ Max.
3. Insulation R.:DC 500V 100M Ω Min.
4. Dielectric Strength:AC 1500V 1 minute.
5. Electrical Life:20,000 make and break cycles at full load.

Open and Close Type ON-OFF

Cap Color : BLACK



1	TOP CAP	ABS	1	
2	BODY	NYLON	1	
3	WASHER	BRASS	1	
4	NUT	BRASS	1	NI
5	BACK CAP	BAKELITE	1	
6	TERMINAL	BRASS	2	AG


Panel Thickness:
5.0mm Max.
