

C.A 6522 - C.A 6524 - C.A 6526

C.A 6532 - C.A 6534 - C.A 6536

GUIDE DE DÉMARRAGE RAPIDE (FR) / QUICK START GUIDE (GB) /  
SCHNELLSTART-ANLEITUNG (DE) / GUIDA DI UTILIZZO RAPIDO (IT) /  
GUÍA DE INICIO RÁPIDO (ES)
















V	$\Omega$	$\rightarrow 0 \leftarrow$	k $\Omega$












MΩ

MΩ Lock

MΩ  $\odot$ /PI/DAR

MΩ VAR



	ALARM		
			
<div data-bbox="84 622 308 790"> <p><b>88.5</b> nF</p> <p>•••))</p> </div>	<p>MΩ</p> <div data-bbox="324 406 548 574"> <p>ALARM &gt; 250 MΩ</p> <p><b>0.0</b> V<sub>AC</sub></p> <p>•••))</p> </div>	<p>kΩ</p> <div data-bbox="565 406 789 574"> <p>ALARM &lt; 1000 kΩ</p> <p><b>5 1.8</b> kΩ</p> <p>•••))</p> </div>	<p>Ω</p> <div data-bbox="806 406 1036 574"> <p>ALARM &lt; 200 Ω</p> <p><b>0.43</b> Ω</p> <p>•••))</p> </div>
<div data-bbox="84 909 308 1013"> <p><b>⊕ C.A 6532</b></p> </div>	  		
<p>40 ← → 60 nF/km</p>  	<p>10V: &lt;10kΩ, &lt;20kΩ, &lt;40kΩ          25V: &lt;25kΩ, &lt;50kΩ, &lt;100kΩ          50V: &lt;50kΩ, &lt;100kΩ, &lt;200kΩ          100V: &lt;100kΩ, &lt;200kΩ, &lt;400kΩ          250V: &lt;250kΩ, &lt;500kΩ, &lt;1MΩ          500V: &lt;500kΩ, &lt;1MΩ, &lt;2MΩ          1000V: &lt;1MΩ, &lt;2MΩ, &lt;4MΩ          VAR: &lt;10kΩ, &lt;50kΩ, &lt;100kΩ</p> <div data-bbox="565 853 789 1021"> <p>ALARM &gt; 500 kΩ</p> <p><b>5 1.8</b> kΩ</p> <p>•••))</p> </div> <div data-bbox="806 853 1036 1021"> <p>ALARM &lt; 100 Ω</p> <p><b>0.43</b> Ω</p> <p>•••))</p> </div> <p>&gt;50kΩ, &gt;100kΩ, &gt;200kΩ      &lt;2Ω, &lt;1Ω, &lt;0.5Ω</p>		
<div data-bbox="84 1133 308 1388"> <p><b>1249</b> km</p> <p><b>62.4</b> nF</p> <p>•••))</p> </div>	<p>Ω C.A 6522</p>		
<div data-bbox="84 1404 308 1492"> <p><b>1249</b> km</p> <p><b>62.4</b> nF</p> <p>•••))</p> </div>	  <div data-bbox="324 1228 548 1396">  <p>ALARM &gt; 250 MΩ</p> <p><b>507</b> MΩ</p> <p>•••))</p> </div> <div data-bbox="806 1316 1036 1484"> <p>ALARM &lt; 200 Ω</p> <p><b>0.43</b> Ω</p> <p>•••))</p> </div>		

MEM	Ⓜ	Ⓜ	P