



Yuasa Technisches Datenblatt

Yuasa YBX3100 - YBX3000 SMF Batterien

Leistung

Spannung	12V
Kapazität 20 Std (vorgegeben)	71Ah
Kaltstartstrom (A) EN1	650A

Abmessungen

Länge	278mm
Breite	175mm
Höhe	175mm

Maße und Gewichte

Durchschnittliches Gewicht inkl. Säure	15.8kg
Gewicht (trocken)	-
Säure Volumen	-



Gehäuseeigenschaften

Gehäusotyp	LB3 DIN
Batteriehälter	B3/B4
Ladezustandsanzeige	✓
Tragegriffe	✓
Entgasung	✓
Semi Traktionseigenschaften	-
Deckel Typ	SMF doppelwandige Deckelkonstruktion


Technologie

Flammschutz	✓
Technologie	Ca/Ca
Separator	PE
VDA Überroll Test	✓
Ladestrom	4A


Anschlusspol Typ

T1

Standard DIN Post




Zellenanordnung



Batteriehälter

B3/B4 (B3 with Hold-Down adaptor)



Ausstellungsdatum: 10/08/2018 - E&EO



Yuasa Technical Data Sheet

Yuasa YBX3100 - YBX3000 SMF Batteries

Performance

Voltage	12V
Capacity (20-hour)	71Ah
Cold Cranking Amps (EN1)	650A

Dimensions

Length	278mm
Width	175mm
Height	175mm

Weights & Measures

Mean Weight with Acid	15.8kg
Dry Weight	-
Acid Volume	-



Container Features

Case Type	LB3 DIN
Hold Down	B3/B4
State of Charge Indicator	✓
Handles	✓
End Venting	✓
Semi-Traction Features	-
Lid Type	SMF Double Lid


Technology

Flame Arrestor	✓
Technology	Ca/Ca
Separator	PE
VDA Roll Over Test	✓
Recommended Charge Rate	4A


Terminal Type

T1

Standard DIN Post




Cell Assembly Layout



Battery Hold-down

B3/B4 (B3 with Hold-Down adaptor)



Data Sheet generated on 10/08/2018 - E&OE