

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0357460210](#)
Status: **Active**
Overview: [VersaBlade Wire-to-Wire Connector System](#)
Description: [VersaBlade Female Crimp Terminal, 14-18 AWG, Type A](#)

Documents:

Drawing (PDF)	Application Specification 351500000ASENG-000 (PDF)
3D Model (PDF)	Application Specification 351500000ASKOR-000 (PDF)
3D Model	Packaging Specification PK-35746-001-001 (PDF)
Product Specification 351800400-001 (PDF)	Datasheet (PDF)
Product Specification 351800600-001 (PDF)	Brochure (PDF)
Product Specification PS-35150-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-35182-003-001 (PDF)	

General

Product Family	Crimp Terminals
Series	35746
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
UPC	800754378468

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.320/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.40mm max.
Wire Size AWG	14, 16, 18
Wire Size mm²	0.85-2.00

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	351500000AS_ENG-000 , 351500000AS_KOR-000
Crimp Specification	CS-35745-001-001 , CS-35745-001-002
Packaging Specification	PK-35746-001-001
Product Specification	351800400-001 , 351800600-001 , PS-35150-001-001 , PS-35182-003-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[35746](#) Series

Use With

VersaBlade Standard Receptacle Housings
[351500300](#) , [351500304](#) , [351500309](#) ,
[351500310](#) , [351500314](#) , [351500319](#) ,
[351503309](#) , [351503319](#) , [351504319](#) ,
[351500400](#) , [351500404](#) , [351500409](#) ,
[351500410](#) , [351500412](#) , [351500414](#) ,
[351500419](#) , [351503419](#) , [351504419](#) ,
[351500600](#) , [351500604](#) , [351500609](#) ,
[351500610](#) , [351500612](#) , [351500614](#) ,
[351500619](#) , [351503609](#) , [351503619](#) ,
[351504619](#)
VersaBlade Standard
Plug Housings [35151](#)
VersaBlade
Multi-Module Receptacle Housings [35180](#)
, [35524](#) , [2026500909](#) , [2041020609](#) ,
[2041020429](#)
 VersaBlade Multi-Module
Plug Housings [351810200](#) , [351810204](#)
, [359650200](#) , [359650204](#) , [359650210](#)
, [359650214](#) , [359659200](#) , [359659203](#) ,
[2041020209](#) , [2041020219](#) , [2041020409](#) ,
[2041020419](#)

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction and Activation Tool	638132700
Hand Crimp Tool for 1.80mm-Wide Crimp Terminals	638190600
T2 Terminator Die	638529100
FineAdjust Applicator for Male and Female VersaBlade Crimp Terminals, 14-18 AWG Wire with Insulation Diameter 2.80-3.40mm for IPC Class 2	638629100

This document was generated on 02/04/2022
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION