

SBU58 series

The SBU58 series of AC/DC switching mode power supplies provide 60 Watts of continuous output power. All supplies are UL 94V-1 min compliant. All models meet FCC Part-15 class B and CISPR-22 class B emission Limits and are designed to comply with UL/c-UL and CE marking conformity assessment. All units are 100% burned in and tested.

RoHS2 2011/65/EU

60W Open Frame Power Supply for General Purpose

FEATURES:

- * Wide Operating Voltage 90 to 264 VAC,47 to 63 Hz
- * Internal EMI filter
- * Crowbar Mode Over Voltage Protection
- * Single Output
- * Class I system
- * 2 years warranty



APPLICATIONS:

- * Monitor
- * Industrial PC
- * Set-top box
- * AV equipment
- * CCD recorder

GENERAL SPECIFICATION:

- * Short Circuit Protection: Auto Recovery
- * Cooling: Free Air Convection
- * Flammability Rating: UL94V-1
- * Protection Classes: Class I
- * Safety: UL 60950-1:2nd Edition, IEC 60950-1:2005 /A2:2013, EN60950-1:2006 /A2:2013, CSA C22.2 NO.60950-1-07



Flectrical Characteristics

c **M**us C E C B (C A

APPROVALS:

| Electi | ical Characteristics: | £1100330 1.2000 /A2.2013, CSA C | | | | |
|--------|---------------------------------------|---|------|---------|---------|-------|
| Symbol | Characteristic | Condition | Min. | Тур. | Max. | Unit |
| Vins | Safety Approval Input Voltage Range | Safety Approval & Specification in Label | 100 | | 240 | VAC |
| Vin | Input Operate Voltage Range | Detail to see Fig.1 | 90 | | 264 | VAC |
| Fi | Input Frequency | Sine wave | 47 | | 63 | Hz |
| Po | Output Power Range | See Rating Chart | | | 60 | W |
| Iil | Low Line Input Current | Full Load, Vin=100VAC | | 1.6 | | Α |
| Iih | High Line Input Current | Full Load, Vin=240VAC | | 0.66 | | Α |
| Irl | Low Line Input Inrush Current | Full Load, 25°C, Cool start, Vin=100VAC | | | 30 | Α |
| Irh | High Line Input Inrush Current | Full Load, 25°C, Cool start, Vin=240VAC | | | 72 | Α |
| Ik | Safety Ground Leakage Current | Vin=240VAC, Fi=60Hz | | | 0.75 | mA |
| η | Efficiency | Full Load, Vin=230VAC, Detail to see Rating Chart | S | ee Rati | rt | |
| △Voi | Line Regulation | Full Load, Vin=100~120VAC | 0.5 | | 1 | % |
| △VoL | Load Regulation | Vin=230VAC, 10~90% Load Change at Condition | 2 | | 5 | % |
| OVP | Over Voltage Protection | Over Voltage Protection | 112 | | 132 | % |
| OLP | Over Load Protection | Recovers automatically after fault condition is removed | 110 | | 150 | % |
| ttr | Time of Transient Response | Io=Full Load to Half Load, Vin=110VAC | | | 4 | ms |
| thu | Hold-Up Time | Full Load, Vin=100VAC | S | ee Rati | ng Chai | rt |
| ts | Start-up time | Full Load, Vin=100~240VAC | | | 2 | S |
| Тс | Temperature Coefficient | Full load, Vin=100~240VAC | | | ±0.04 | %/°C |
| HV | Dielectric Withstanding Voltage (P-S) | Primary to Secondary | | | 4242 | VDC |
| Vpg | Dielectric Withstanding Voltage (P-G) | Primary to PE | | | 2121 | VDC |
| EMI | EMC Emission | Compliance to EN55022 (CISPR22) | | | В | Class |

Environmental:

| Symbol | Characteristic | Condition | Min. | Тур. | Max. | Unit |
|--------|--------------------------------|--|------|------|------|------|
| То | Operating Temperature | Detail to see Fig.2 (Derate linearly from 100% load at 50°C to 50% load at 70°C) | 0 | | 70 | °C |
| Ts | Storage Temperature | 10 ~ 95% RH | -40 | | 85 | °C |
| Но | Operating Humidity | non-condensing | 0 | | 95% | RH |
| Hs | Storage Humidity | | 0 | | 95% | RH |
| ESDa | Electro Static Discharge | Air Discharge, IEC61000-4-2 | | | 8 | kV |
| ESDc | Electro Static Discharge | Contact Discharge, IEC61000-4-2 | | | 4 | kV |
| MTBF | Mean Time Between Failure | Operating Temperature at 25°C, Calculated per MIL-HDBK-217F | 100k | | | h |
| ELEV | Operating Altitude (Elevation) | All condition | | | 2000 | m |
| VBR | Vibration | 10 ~ 500Hz, 10min./1cycle, 60min. each along X, Y, Z axes | | | 5 | G |
| Vsl | Surge Voltage | Line-Neutral | | | 1 | kV |
| Vsg | Surge Voltage | Line-PE & Neutral-PE | | | 2 | kV |

General

9SINPRO


SBU58 series


V1.

SPECIFICATION NOTE:


- 1. Output can provide up to peak load when the power supply starts up. Continuous staying in more than rated load is not allowed.
- 2. At factory, in 60% rated load condition, each output is checked to be within voltage accuracy.
- 3. Line regulation is defined by changing $\pm 10\%$ of input voltage from nominal line at rated load.
- 4. Load regulation is defined by changing $\pm 40\%$ of measured output load from 60% rated load.
- The ripple is measured from peak to peak with a bandwidth-limit of 20MHz (Measured at the output connector with a 0.1uF ceramic capacitor and a 47uF electrolytic capacitor).
- 6. Hold up time is measured from the end of the last charging pulse to the time which the main output drops down to low limit of main output at rated load and nominal line.
- 7. Efficiency is measured at rated load, and nominal line.

MECHANICAL DIMENSIONS: (UNIT: mm[inch])





60W Open Frame Power Supply for General Purpose



P/N:SBU58-XXX-H3 (Standard) or SBU58-XXX-H4 (Optional)

| | H3 (Standard) | H4 (Optional) |
|----------------|------------------|------------------|
| MOUNTING HOLES | 3,2±0,5 | 4.0±0.5 |
| Α | 3.15±0.5 | 4.3±0.5 |
| В | 95.3±0.5 | 93.0±0.5 |
| С | 3.15±0.5 | 4.0±0,5 |
| D | 44.5±0.5 | 42.8±0.5 |

PACKING:

- 1. Dimensions are shown in mm.
- 2. Weight: 140gs approx.
- 3. Input connector mates with JST housing VHR-3N and JST SVH series crimp terminal.
- ${\bf 4.\ Output\ connector\ mates\ with\ JST\ housing\ VHR-6N\ and\ JST\ SVH\ series\ crimp\ terminal.}$

PIN CHART

| MODEL PIN | 1 | 2 | 3 | 4 | 5 | 6 |
|-----------|-----|-----|-----|-----|-----|-----|
| SBU58-1XX | оит | OUT | OUT | RTN | RTN | RTN |

Rating Chart:

| MODEL NO. | Setting Voltage Range (Factory setting, can't be adjusted) | | Output Current (Based on the output volt.) | | Maximum Output Power | Ripple & No | Total Regulation | Typ. Efficiency | Typ. No Load Consumption | Hold-Up Time | Protection |
|------------|---|-------|---|------|-------------------------|-------------|------------------|-----------------|-----------------------------|--------------|------------|
| | min | max | min | max | ver | Noise | tion | псу | ion | me | Mode |
| | (VDC) | (VDC) | (A) | (A) | (W) | (mVp-p) | (%) | (%) | (W) | (ms) | e e |
| *SBU58-102 | 5.0 | 6.0 | 6.66 | 8.00 | 40 | 60 | ±5 | 76.5 | 0.5 | 12 | Hiccup |
| *SBU58-103 | 6.0 | 8.0 | 6.00 | 8.00 | 48 | 80 | ±5 | 76.5 | 0.5 | 12 | Hiccup |
| SBU58-104 | 8.0 | 11.0 | 5.00 | 6.87 | 55 | 110 | ±5 | 76.5 | 0.5 | 12 | Hiccup |
| SBU58-105 | 11.0 | 13.0 | 4.61 | 5.45 | 60 | 130 | ±5 | 84 | 0.5 | 12 | Hiccup |
| SBU58-106 | 13.0 | 16.0 | 3.75 | 4.61 | 60 | 160 | ±5 | 85 | 0.5 | 12 | Hiccup |
| SBU58-107 | 16.0 | 21.0 | 2.85 | 3.75 | 60 | 200 | ±5 | 85 | 0.5 | 12 | Hiccup |
| SBU58-108 | 21.0 | 27.0 | 2.22 | 2.85 | 60 | 180 | ±3 | 85.5 | 0.5 | 12 | Hiccup |
| SBU58-109 | 27.0 | 33.0 | 1.81 | 2.22 | 60 | 200 | ±3 | 85.5 | 0.5 | 12 | Hiccup |
| *SBU58-110 | 33.0 | 40.0 | 1.50 | 1.81 | 60 | 300 | ±3 | 86 | 0.5 | 12 | Hiccup |
| SBU58-111 | 40.0 | 48.0 | 1.25 | 1.50 | 60 | 300 | ±2 | 87.5 | 0.5 | 12 | Hiccup |

 $^{[*] = \}mathsf{MOQ} \ \mathsf{is} \ \mathsf{required}. \ \mathsf{Please} \ \mathsf{contact} \ \mathsf{sales}.$