

TORCIA ATEX

Torcia a sicurezza intrinseca per utilizzo in ambienti pericolosi
Intrinsically safe flashlight for use in hazardous locations
 Lampe-torche LED à sécurité intrinsèque pour utilisation en milieux dangereux
 Linterna LED intrínsecamente segura para su uso en entornos peligrosos
 LED ATEX-Sicherheitstaschenlampe für die Nutzung in gefährlichen Orten



FATEX01



PACKING	INNER	MASTER
Blister F6	pcs 6	pcs 48

CLASSIFIED UL US	UL USA : UL FILE NO.: OERX.E324236 Class I Div 1 & 2 Grp ABCD Class II Div 1 & 2 Grp EFG Class III Temp Code: T4
	IECEx Worldwide : IECEx CERTIFICATE NO.: IECEx UL 11.0042X Ex ia IIC T4 Ga
	Ex Europe : ATEX CERTIFICATE NO.: DEMKO 11 ATEX 1110052X II 1G Ex ia IIC T4 0518



DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

Codice / Item / Code / Código / Code	FATEX01
Nome prodotto / product name / Nom du produit / Designación / Produktname	TORCIA ATEX
Alimentazione / Power supply / Alimentation / Alimentación / Stromversorgung	-
Batteria / Battery / Batterie/ Batería / Batterie	4 x AA (not included)
Tempo di ricarica / Charging Time / Temps de recharge / Tiempo de carga / Ladezeit	-
Autonomia / Runtime / Autonomie / Autonomía / Leuchtdauer	14 hrs
Tecnologia della Luce / Light technology / Technologie de la lumière / Tecnología de iluminación / Leuchtentechnologie	1W OSRAM HIGH POWER LED
Potenza d'illuminazione (W) / (W) Power / Puissance (W) / Potencia (W) / Leuchtstärke (W)	
Consumo elettrico (W) / (W) Consumption / Consommation (W) / Consumo (W) / Verbrauch (W)	
Lumen / Lumen / Lumen / Lumen / Lumen	60 Lm
Tipo di luce / Kelvin degrees / Degrés Kelvin / Temperatura de luz / Grad Kelvin	
IRC / Colour rendering Index / Indice de rendu des couleurs / IRC / Farbwiedergabeindex	
Fascio di luce / Light beam / Type de faisceau / Tipo de haz / Lichtstrahl	Focus light
Portata / Range / Distance d'éclairage / Alcance alumbrado / Leuchtweite	130 mt
Durata di vita del LED / LED Life time / Durée de vie des LED / Durada de vida del LED / Lebensdauer LED	
Massima intensità del fascio / Peak beam intensity / Intensité maximale du faisceau / Máxima intensidad / Abstrahlintensität	50000 hrs
Dimmerabilità / Dimmable / Dimmable / Dimmer, regulador / Dimmereigenschaften	
Numero di cicli on-off / On off cycles / Nr de cycles on-off / Numero de On-OFF / Ein-Aus Zyklen	
Power factor / Power factor / Power factor / Power factor / Leistungsfaktor	
Resistenza Meccanica / Mechanical resistance / Résistance Mécanique / Resistencia mecanica / Mechanische Widerstandsfähigkeit	
Cavo / Cable / Câble / Cable / Kabel	-
Materiale / Material / Materiau / Material / Material	ABS
Grado di protezione / Protection degree / Degré de protection / Estanqueidad / Schutzgrad	IP67
Accessori inclusi / Accessories included / Accessoires fourni / Accesorios incluidos / Zubehör enthalten	
Funzioni / Functions / Fonctions / Función / Funktionen	
Dimensioni prodotto / Product dimensions / Dimensions du produit / Dimensiones producto / Abmessungen Produkt	Width x Height x Length: 175 x 45 x 45 mm
Dimensioni prodotto imballato / Packed dimensions / Dimensions du produit emballé / Dimensiones embalaje / Abmessungen Umverpackung	Width x Height x Length: 100 x 325 x 50 cm
Peso netto / Net Weight / Poids net / Peso neto / Gewicht netto	105 g
Peso prodotto imballato / Weight of packaged product / Poids du produit emballé / Peso producto con embalaje / Gewicht mit Umverpackung	185 g