


Battery air compressor TX-157







Up to 8 bar maximum pressure



Work lamp with 6 LEDs



4 adapters for all valve types



Large display for setting/ reading the pressure



4 pressure units selectable (PSI, BAR, KPA, KG/CM²)



Storage bag made of EVA material



Aluminium housing















Digital pressure display, desired pressure adjustable Auto Off function when the set pressure is reached Storage bag

Output power max. 15L/min.

Max. pressure 8bar

Hose incl. valve adapter, ball needle, bicycle adapter and nozzle set for large air openings

Technical Specifications:

• Weight / Dimensions: 0.75 kg / (L) 7 x (W) 7,3 x (H) 28.9cm

Package Contents:

Technaxx Battery air compressor TX-157, Connection cable for the cigarette lighter and USB Kabel, User Manual

Article No. 4906

