


Copying of this document and giving it to others,
 and the use or communication of the contents thereof,
 are forbidden without express authority. All rights reserved.



RED CONNECT "+", BROWN CONNECT "-" THE PLUNGER MOVE DOWN	
RED CONNECT "+", WHITE CONNECT "-" THE PLUNGER MOVE UP	24V
RED CONNECT "+", BLUE CONNECT "-" THE PLUNGER MOVE DOWN	
RED CONNECT "+", WHITE CONNECT "-" THE PLUNGER MOVE UP	12V

NOTE:

1. 150W
2. storke 22mm, force>10N;
3. 0mm stroke, Pe-force>60N ;
4. DUTY 10%

Weitergabe und Vervielfältigung dieser Unterlage, sowie
 Verwertung und Mitteilung ihres Inhalts nicht gestattet,
 soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten

	Maße in mm Dimensions in millimeters	Zul. Abw. f. Maße ohne Toleranzang. General tolerances	Fertigzustand finished cond.	Maßstab Scale 1:1	Menge Quantity 1
		ISO 2768-Km		Rohstoff/Raw material - Rohteil-Nr./Raw piece No. - Werkzeug-Nr./Tool No. -	
		20 14 Datum Date	F. Käsbauer Name Name	Benennung/Designation	
		26.03.14 Bearb. Drawn		Doppelspulenhubmagnet 22mm stroke length	
		26.03.14 Gepr. Check	A. Huber		
				Sachnummer/Part-No.	
				ITS-LX-3931-__ VDC	
Ausg. Issue	Änderung Modification	Datum Date	Name Name	Ursprung Source	Blatt Sheet 1 von of 1