

PORTABLE DAB+/FM RADIO
WITH BUILT-IN BATTERY




HPG 335DAB



- DAB+/FM radio with RDS
- LCD display (with backlight)
- Built-in rechargeable battery (up to 8 hours)
- Buttons for: power, mode, menu/info/back, preset/scan, channel (up/down), enter and volume
- Metal telescopic antenna
- Dual alarm clock function
- Sleep time function
- Built-in 3.5mm Jack headphone socket
- Charged by USB (input: 5V • USB charge cable incl.)
- Size: 162(W) x 53(D) x 102(H)mm



- Radio DAB+/FM avec RDS
- Écran LCD (avec rétro-éclairage)
- Pile rechargeable intégrée (jusqu'à 8 heures d'autonomie)
- Boutons de : puissance, mode, veille/info, présélection/scan, canal (vers le haut/vers le bas), entrée et volume
- Antenne télescopique en métal
- Fonction double réveil
- fonction de temps de sommeil
- Prise 3,5 mm intégrée pour casque
- Chargée via le port USB (Câble de charge USB inclus)
- Dimensions : 162(L) x 53(P) x 102(H)mm



Telescopic adjustable antenna



High resolution display



3.5mm Jack headphone socket

PORTABLE DAB+/FM RADIO
WITH BUILT-IN BATTERY




HPG 335DAB



- DAB+/UKW Radio mit RDS
- LCD-Display (mit Hintergrundbeleuchtung)
- Eingebaute wiederaufladbare Batterie- (hält bis zu 8 Stunden)
- Tasten: power, modus, menu/info/zurück, preset/scan, kanal (hoch/runter), enter und lautstärke
- Teleskopantenne aus Metall
- Doppelte Weckerfunktion
- Eingebauter 3,5 mm Klinke Kopfhöreranschluss
- USB-Auładefunktion (Eingangsleistung: 5V • USB-Ladekabel im Lieferumfang enthalten)
- Größe: 162(B) x 53(T) x 102(H)mm



- DAB+/FM radio met RDS
- LCD display (van achteruit verlicht)
- Ingebouwde oplaadbare batterij (tot 8 uur)
- Knoppen voor: power, modus, menu/info/back, preset/scan, kanaal (op/neer), enter en volume
- Metalen telescopische antenne
- Dubbele wekker-functie
- Ingebouwde 3.5mm Jack hoofdtelefoon aansluiting
- Laden via USB (input: 5V • USB laadkabel inbegrepen)
- Afmetingen: 162(B) x 53(D) x 102(H)mm



Telescopic adjustable antenna



High resolution display



3.5mm Jack headphone socket