

**Artikel Nr.: 620119**

Schienensystem 3-Phasen 230V, Draconis, Weißaluminium RAL 9006, 220-240V AC/50Hz, 45W/ 55W/ 72W, Warmweiß + Neutralweiß



**Technische Daten**

**Charakteristik**

<b>Material</b>	Aluminium Druckguss
<b>Farbe</b>	Weißaluminium RAL 9006
<b>Optik</b>	
<b>im Lieferumfang</b>	Draconis Deckenaufbauleuchte Draconis 3-Phasen Adapter

**Elektrische Daten**

<b>Leistung</b>	45W/ 55W/ 72W
<b>Eingangsspannung</b>	220-240V AC/50Hz
<b>Eingangsstrom</b>	
<b>Fassung / Sockel</b>	
<b>Anzahl Sockel</b>	
<b>Netzgerät</b>	inkl. LED-Netzgerät
<b>Ansteuerung</b>	nicht dimmbar
<b>Anschlussmöglichkeit</b>	Klemme
<b>Schutzklasse I, II, III</b>	I

**Lichttechnische Eigenschaften**

<b>Leuchtmittel</b>	LED-Modul fest
<b>Lichtfarbe</b>	Warmweiß + Neutralweiß
<b>Farbtemperatur</b>	2700 / 3500 / 4000 K
<b>Lichtstrom</b>	8215 lm
<b>Abstrahlwinkel</b>	60°
<b>LED Typ</b>	SMD
<b>LED Anzahl</b>	198
<b>Strahlungsverteilung</b>	582 nm



## Artikel Nr.: 620119

Schienensystem 3-Phasen 230V, Draconis, Weißaluminium RAL 9006, 220-240V AC/50Hz, 45W/ 55W/ 72W, Warmweiß + Neutralweiß

### Lichtrichtung

Dreh- und Schwenkbereich	feststehend
Neigungswinkel	
Abstrahlverhalten	
Reflektor / Linse	



### Abmessungen und Gewicht

Länge	577,60
Breite	188,60
Höhe	128,70
Durchmesser	0,00
Gewicht	2634 g

### Grenzwerte

Die Überschreitung der Grenzwerte und Betriebsspannung führt zu einer starken Verkürzung der Lebensdauer sowie Zerstörung der LED Module.

Betriebstemperatur	-20°C - +30°C
Lagertemperatur	-30°C - +60°C
IP - Schutzart	IP20



**Artikel Nr.: 620119**

Schienensystem 3-Phasen 230V, Draconis, Weißaluminium RAL 9006, 220-240V AC/50Hz, 45W/ 55W/ 72W, Warmweiß + Neutralweiß




**Allgemeine Eigenschaften**

**Umwelteigenschaften**

<b>Energieeffizienzklasse</b>	A+
<b>Energieverbrauch</b>	72 kWh/1000h

**Lebensdauer**

<b>Lebensdauer</b>	50000 h
<b>Lichtstrom Ende Lebensdauer</b>	0,70
<b>Schaltzyklen</b>	25000

<b>IP20</b>	Schutz gegen das Eindringen von Fremdkörper > 50 mm. Kein Schutz gegen das Eindringen von Wasser.
	Leuchte der Schutzklasse I bei der der Schutz gegen elektrischen Schlag nicht allein auf der Basisisolierung beruht, sondern die eine zusätzliche Sicherheitsvorkehrung derart enthält, dass berührbare leitfähige Teile mit Mitteln zum Anschluss an den Schutzleiter der festen Installation ausgerüstet sind, so dass im Fehlerfall der Basisisolierung berührbare leitfähige Teile nicht aktiv werden können.
	Aufgrund des komplexen Herstellungsprozesses von LED stellen die angegebenen Werte nur rein statistische Größen dar und müssen nicht zwingend den tatsächlichen Parametern jedes einzelnen LED-Moduls entsprechen, sondern können von den typischen Werten abweichen.
	Die Lichtquelle dieser Leuchte darf nur vom Hersteller oder einem von ihm beauftragten Servicetechniker oder einer vergleichbar qualifizierten Person ersetzt werden

## Article no.: 620119

Track system 3-Phases 230V, Draconis, White aluminium RAL 9006, 220-240V AC/50Hz, 45W/ 55W/ 72W, warm white + neutral white



### Technical Data

#### General Characteristics

<b>Material</b>	aluminum die casting
<b>Colour</b>	White aluminium RAL 9006
<b>Optics</b>	
<b>included in delivery</b>	Draconis surface mounted ceiling lamp Dracon 3-phases adapter

#### Electrical Characteristics

<b>Power</b>	45W/ 55W/ 72W
<b>Input Voltage</b>	220-240V AC/50Hz
<b>Input current</b>	
<b>Base (standard designation)</b>	
<b>Number of Bases</b>	
<b>Power supply unit</b>	incl. LED-power supply unit
<b>Electronically reversible</b>	not dimmable
<b>Connection possibility</b>	clamp
<b>Protection class I, II, III</b>	I

#### Light Technical Data

<b>Bulb</b>	LED-module fixed
<b>Colour Designation</b>	warm white + neutral white
<b>Colour temperature</b>	2700 / 3500 / 4000 K
<b>Luminous flux</b>	8215 lm
<b>Beam angle</b>	60°
<b>LED type</b>	SMD
<b>LED quantity</b>	198
<b>Spectral power distribution</b>	582 nm



## Article no.: 620119

Track system 3-Phases 230V, Draconis, White aluminium RAL 9006, 220-240V AC/50Hz, 45W/ 55W/ 72W, warm white + neutral white

### Light Direction

Rotating and tilting range	fixed
Angle of inclination	
Radiation direction	
Reflector / lense	



### Dimensions & Weight

Length	577,60
Width	188,60
Height	128,70
Diameter	0,00
Product Weight	2634 g

### Absolute maximum ratings

The LED will get damaged and the lifetime will decrease when you overrun absolute maximum ratings.

Working temperature	-20°C - +30°C
Storage temperature	-30°C - +60°C
IP - Code	IP20



## Article no.: 620119

Track system 3-Phases 230V, Draconis, White aluminium RAL 9006, 220-240V AC/50Hz, 45W/ 55W/ 72W, warm white + neutral white

### General product data

#### Environmental Characteristics

Energy label	A+
Energy consumption	72 kWh/1000h

#### Lifespan

Lamp life time	50000 h
Luminous flux (end of lifetime)	0,70
Number of switching cycles	25000

**IP20** Protection against penetration of foreign objects > 50 mm. No protection against penetration of water.



Lightings of Protection Class I in which the protection against electric shock is not based solely on isolation, but an additional safety measure contains such a way that accessible conductive parts are equipped with means for connection to the protective conductor of the fixed installation, so that in case of failure of the basic insulation exposed conductive parts cannot be active.



Because of the complex manufacturing process of the LED the above shown data are just a statistical size, which is not forced to be the realistic data of every LED.



The light source of this luminaire may only be replaced by the manufacturer or by a service technician appointed by him or by a comparable qualified person