


# Data Sheet

powered by  
RICH BAY



**EMPLOYER UNIQUEMENT  
AVEC UN FUSIBLE DE 250V  
USE ONLY WITH A 250V FUSE**




**RICH BAY  
R-3014S  
max. 2.5W  
10A/250V**




**PANEL CUT-OUT**

**SPECIFICATION: (SWITCH)**

XX	A
10	1.0
15	1.5
20	2.0

1. Electrical rating : 6A 250VAC & 12A 125VAC [UL]  
4(1)A 250VAC [VDE . ENEC10]
2. Contact resistance : <20mΩ (Initial)
3. Insulation resistance : 100MΩ (500VDC between open contacts)
4. Dielectric strength : 1500V 1 minute

Rating:AC 15A 250V	
Mark	Safety Regulation
	CULUS
Rating:AC 10A 250V	
Mark	Safety Regulation
	VDE
	ENEC

 UNIT mm	UNIT QTY	SCALE	TOLERANCE	X.XX±0.1 XX.XX±0.2 XXX.XX±0.3	PRODUCT NO.	R-3014S (01) XX	REV
	1	1:1					
DRAWN BY:  109.10.12 林文啟	APPROVED BY:  109.10.12 張育誠	ID NO	210218A10	INTERIM NO.			J
		DESCRIPTION		NEW NO.			