

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5600201120

Status:

Active

Overview:

DuraClik Connector System

Description:

DuraClik Wire-to-Board Header, Single Row, Vertical, 11 Circuits, Tin (Sn) Plating, Natural

Documents:

3D Model (PDF)

Packaging Specification PK-560020-002-JP-001 (PDF)

Drawing (PDF)


Datasheet (PDF)

3D Model

RoHS Certificate of Compliance (PDF)

Product Specification PS-502351-001-001 (PDF)

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	560020
Application	Automotive, Signal, Wire-to-Board
Comments	The Operating Temperature Range when used with DuraClik series 502351 is -40°C to +105°C. It is -40°C to 125°C when used with DuraClik ISL series 560123 or TPA series 505151.
Overview	DuraClik Connector System
Product Name	DuraClik
UPC	887191747378
Physical	
Breakaway	No
Circuits (Loaded)	11
Circuits (maximum)	11
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	SC-0
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Resin	Polyamide
Net Weight	1.267/g
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C, -40° to +125°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	3.0A



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

560020 Series

Mates With

DuraClik Crimp Housings [502351](#) , [560123](#) , [505151](#)

Voltage - Maximum	125V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-560020-002-JP-001
Product Specification	PS-502351-001-001
Sales Drawing	SD-560020-001-001, SD-560020-003-001

This document was generated on 02/02/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION