

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0008500108

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK 396 Crimp Terminal 2578, 22-26 AWG, Bag, Brass, 2.540µm Tin (Sn)

Documents:	
Drawing (PDF)	Packaging Specification PK-2759-001-001 (PDF)
Product Specification PS-08-50-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	2578
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	KK Interconnect Solutions
Packaging Alternative	08500107 (Reel)
Product Name	KK 396, KK 508
UPC	800754314473
Physical	
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.150/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65mm max.
Wire Size AWG	22, 24, 26
Wire Size mm²	N/A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	2578-(P909)L
Reference - Drawing Numbers	
Packaging Specification	PK-2759-001-001
Product Specification	PS-08-50-001
Sales Drawing	SD-2578-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

2578 Series

Use With

2574 , 2139 , 41695 , 3069 , 6422 , 5265 , 5239

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals PremiumGrade Hand	11030016
Crimp Tool for KK 3.96mm Terminals, 22-26 AWG	638117400

This document was generated on 11/24/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION