

## Features

- Compliant to DoE 2016 (Level VI)
- ErP Stage 2, NRCAN & GEMS Level VI
- No Load Power Consumption < 0.1 W
- LPS – Limited Power Source
- Regulated Output with Low Ripple Noise
- 1 Year Warranty

## Marks / Approvals



Product similar to photo, variations possible.

## Specifications

	MODEL	Voltage	Min. Load	Max. Load	Max. Power
	ATS 090-P120	12 V	0.00 A	7.00 A	84 W
	ATS 090-P150	15 V	0.00 A	6.00 A	90 W
	ATS 090-P160	16 V	0.00 A	5.63 A	90 W
	ATS 090-P180	18 V	0.00 A	5.00 A	90 W
	ATS 090-P190	19 V	0.00 A	4.74 A	90 W
	ATS 090-P200	20 V	0.00 A	4.50 A	90 W
	ATS 090-P240	24 V	0.00 A	3.75 A	90 W
	ATS 090-P300	30 V	0.00 A	3.00 A	90 W
INPUT	<b>Voltage</b>	AC 100 V – 240 V			
	<b>Frequency</b>	50 Hz - 60 Hz			
	<b>Current</b>	1.2 A max.			
	<b>Protection</b>	Internal Primary Current Fuse, Inrush Limiting			
OUTPUT	<b>Load Regulation</b>	± 5 % (typical)			
	<b>Ripple</b>	1 % – 2 % V p-p max. for output voltage at full load			
	<b>Transient Response</b>	0.5 ms for 50 % load change typical			
	<b>Leakage Current</b>	0.25 mA max.			
	<b>Protection</b>	Short circuit Protection • Over Voltage Protection • Over Current Protection			
OTHERS	<b>Cooling</b>	Convection			
	<b>Efficiency</b>	DoE Level VI • Energy Star • ErP Stage 2 • NRCAN & GEMS Level VI Certified			
	<b>Holdup Time</b>	10 ms at full load			
	<b>Dielectric Withstand</b>	AC 3000 V Primary – Secondary			
	<b>MTBF</b>	300,000 calculated hours at 25 °C by telcordia SR-332			
ENVIRONMENT	<b>Temperature</b>	Operating: 0 °C – 40 °C / Storage: -20 °C – 80 °C			
	<b>Humidity</b>	Operating: 20 % RH – 80 % RH / Storage: 10 % RH – 90 % RH			
<b>EMI Conduction &amp; Radiation</b>	Compliance to EN 55022 Class B				
<b>Harmonic Current</b>	Compliance to EN 61000-3-2, -3				
<b>EMS Immunity</b>	Compliance to IEC 61000-1-2, -3, -4, -5, -6, -8, -11				
<b>Approvals</b>	IEC / EN / UL 62368-1 • IEC / EN / UL 60950-1 • CE • RCM • PSE • BSMI • CCC • FCC • LPS				
<b>Case Dimensions</b>	151 mm × 64 mm × 36 mm (C14 version)				
<b>Weight</b>	460 g				