


6005-IEC

Designation: Pincer Clip w/ 4 mm Banana (female) Jack (socket). Flexible shaft.

Applications: to grasp conductive parts safely to measure voltages. General purpose electric and electronic testing, controlling, and measuring.





## DATA SHEET (page 2 of 2).

6005-IEC

Designation: Pincer Clip w/ 4 mm Banana (female) Jack (socket). Flexible shaft.

Electrical safety 1000 V CAT II

1000 V CAT II, reinforced insulation, 6 A (at +40 °C). According to EN / IEC 61010-031:2015.

The pincer clip shall not be used in

CAT III and CAT IV environments.

The conductive end is too long to

comply with the CAT III and CAT IV.

The pincer clip is rated to the

CAT II only. Unfortunately the

length of the conductive end

furthers short-circuits between

electric potentials. While the

CAT III and CAT IV include higher

electric energy than the CAT II. The

combination of higher probability

of short-circuit and higher hazard

in case of short-circuit with the

CAT III and CAT IV limits the pincer

clip to the CAT II only.

These specifications come from the creepage distances, clearances, accessible parts, and solid insulation of the clip. And the considered specifications of the environment are:

pollution degree, 1 or 2;

relative humidity, 80 % maximum for temperatures up to 31 °C decreasing linearly to 50 % relative humidity at +40 °C;

temperature range, +5 °C to +40 °C;

indoor use; and

altitude, 2000 m maximum.

-20 °C mini., +60 °C maxi. (please see above too).

Contact us at:

sales@electro-pip.com

+33(0) 384 821 330

www.electro-pjp.com

**ELECTRO-PJP** 

ZI ((Charmes d'Amont)) 13 rue de Madrid **39500 TAVAUX** FRANCE

Operating temperature range · European Directive "Low Voltage Directive" 2014/35/UE. Conformity · International / European standard EN / IEC 61010-031:2015. · European Directive "RoHS" 2011/65/EU. European REACH regulation n°1907 / 2006. • "RoHS" compliant, Pb ≤ 4 % in conductor, Pb ≤ 0.1 % in insulator, Hg ≤ 0.1 %, Environment Cr VI  $\leq$  0.1 %, Cd  $\leq$  0.01 %, PBB  $\leq$  0.1 %, and PBDE  $\leq$  0.1 %. · REACH compliant, no substances from the candidate list of SVHC for authorisation at mass concentrations greater than 0.1 %. Conductors: nickel-coated steel, steel, and brass. Insulators: please contact us. Materials Colors Black Yellow Green White 0.019 kg. Weight Designed and manufactured in France. Origin Reliability benchmark Year of 1st placing on the market 1995.

**GLOSSARY:** 

ACCESSIBLE. Able to be touched with a standard test finger or test pin.

BASIC INSULATION. Insulation of HAZARDOUS LIVE parts which provides basic protection.

CAT II. Measurement or overvoltage category II. For measurement performed on / equipment connected to the building wiring.

CAT III. Measurement or overvoltage category III. For measurement performed on / equipment connected to part of a building wiring installation

CAT IV. Measurement or overvoltage category IV. For measurement performed on / equipment connected to the origin of the electrical supply to a

CLEARANCE. Shortest distance in air between two conductive parts.

CREEPAGE DISTANCE. Shortest distance along the surface of a solid insulating material between two conductive parts

CTI. Comparative Tracking Index of the insulating material in accordance

DOUBLE INSULATION. Insulation comprising both BASIC INSULATION and SUPPLEMENTARY INSULATION.

EN / IEC 60529, European / international standard regarding the degrees of protection provided by enclosures.

EN / IEC 61010-1. European / international standard regarding the safety requirements for electrical equipment for measurement, control, and laboratory use - Part 1: General requirements.

EN / IEC 61010-031. European / international standard regarding the safety requirements for electrical equipment for measurement, control and laboratory use - Part 031; Safety requirements for hand-held probe assemblies for electrical measurement and test.

"LVD". European Directive 2014/35/EU on the harmonization of the laws of Member States relating to electrical equipment designed for use within certain voltage limits. (Usually called the Low Voltage Directive.)

MAINS. Low-voltage electricity supply system to which the equipment concerned is designed to be connected for the purpose of powering the

MAINS CIRCUIT. Circuit which is intended to be directly connected to the MAINS for the purpose of powering the equipment.

OVERVOLTAGE CATEGORY. Numeral defining a TRANSIENT

POLLUTION. Addition of foreign matter, solid, liquid or gaseous (ionized gases), that may produce a reduction of dielectric strength or surface

POLLUTION DEGREE. Numeral indicating the level of POLLUTION that may be present in the environment.

POLLUTION DEGREE 1. No POLLUTION or only dry, non-conductive POLLUTION occurs, which has no influence.

POLLUTION DEGREE 2. Only non-conductive POLLUTION occurs except that occasionally a temporary conductivity caused by condensation is

REINFORCED INSULATION. Insulation which provides protection against electric shock not less than that provided by DOUBLE INSULATION.

"RoHS" European Directive 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

SOLID INSULATION. Insulating materials.

SUPPLEMENTARY INSULATION Independent insulation applied in addition to BASIC INSULATION in order to provide protection against electric shock in the event of a failure of BASIC INSULATION.

TRANSIENT OVERVOLTAGE. Short duration overvoltage of a few nilliseconds or less, oscillatory or non-oscillatory, usually highly damped.

WORKING VOLTAGE. Highest r.m.s. value of the a.c. or d.c. voltage across any particular insulation which can occur when the equipment is