

**Artikel Nr.: 346032**

Tischleuchte, Kopf Magnetleuchte Miram Schwarz, Schwarz, 3,7V DC, Warmweiß

**Technische Daten**

**Charakteristik**

Material	Aluminium Druckguss
Farbe	Schwarz
Optik	
im Lieferumfang	inkl. 2x2200 mAh Lithium Akku inkl. USB C Ladekabel



**Elektrische Daten**

Leistung / Leistungsaufnahme	/ 2,20 W
Eingangsspannung	3,7V DC
Eingangsstrom	
Fassung / Sockel	
Anzahl Sockel	
Netzgerät	exkl. LED-Netzgerät
Ansteuerung	Touch-Sensor dimmbar
Anschlussmöglichkeit	USB-C
Schutzklasse I, II, III	III

**Lichttechnische Eigenschaften**

Leuchtmittel	LED-Modul fest
Lichtfarbe	Warmweiß
Farbtemperatur	3000 K
Lichtstrom	196 lm
Abstrahlwinkel	47°
LED Typ	SMD
LED Anzahl	20
Strahlungsverteilung	588 nm



**Artikel Nr.: 346032**

Tischleuchte, Kopf Magnetleuchte Miram Schwarz, Schwarz, 3,7V DC, Warmweiß

**Lichtrichtung**

Dreh- und Schwenkbereich	feststehend
Neigungswinkel	
Abstrahlverhalten	
Reflektor / Linse	asymmetrisch


**Abmessungen und Gewicht**

Länge	0,00
Breite	0,00
Höhe	30,00
Durchmesser	120,00
Gewicht	326 g

**Grenzwerte**

Die Überschreitung der Grenzwerte und Betriebsspannung führt zu einer starken Verkürzung der Lebensdauer sowie Zerstörung der LED Module.

Betriebstemperatur	-20°C - +45°C
Lagertemperatur	-40°C - +60°C
IP - Schutzart	IP54



## Artikel Nr.: 346032

Tischleuchte, Kopf Magnetleuchte Miram Schwarz, Schwarz, 3,7V DC, Warmweiß

### Allgemeine Eigenschaften

#### Umwelteigenschaften

Energieeffizienzklasse	
Energieverbrauch	

#### Lebensdauer

Lebensdauer	30000 h
Lichtstrom Ende Lebensdauer	
Schaltzyklen	15000

**IP54** Schutz gegen das Eindringen von Staub. (Staubschutz) Geschützt gegen Spritzwasser.



Leuchte der Schutzklasse III  
Leuchte, bei der der Schutz gegen elektrischen Schlag auf der Anwendung der Schutzkleinspannung (SELV) beruht und in der Spannungen höher als SELV nicht erzeugt werden.



Aufgrund des komplexen Herstellungsprozesses von LED stellen die angegebenen Werte nur rein statistische Größen dar und müssen nicht zwingend den tatsächlichen Parametern jedes einzelnen LED-Moduls entsprechen, sondern können von den typischen Werten abweichen.



Die Lichtquelle dieser Leuchte darf nur vom Hersteller oder einem von ihm beauftragten Servicetechniker oder einer vergleichbar qualifizierten Person ersetzt werden

**Article no.: 346032**

Table lamp, Head Magnetic Light Miram Black, Black, 3,7V DC, warmwhite

**Technical Data****General Characteristics**

Material	aluminum die casting
Colour	Black
Optics	
included in delivery	incl. 2x2200 mAh lithium battery incl. USB C charger cable

**Electrical Characteristics**

Power / power consumption	/ 2,20 W
Input Voltage	3,7V DC
Input current	
Base (standard designation)	
Number of Bases	
Power supply unit	excl. LED-power supply unit
Electronically reversible	touch switch dimmable
Connection possibility	USB-C
Protection class I, II, III	III

**Light Technical Data**

Bulb	LED-module fixed
Colour Designation	warmwhite
Colour temperature	3000 K
Luminous flux	196 lm
Beam angle	47°
LED type	SMD
LED quantity	20
Spectral power distribution	588 nm



**Article no.: 346032**


Table lamp, Head Magnetic Light Miram Black, Black, 3,7V DC, warmwhite

**Light Direction**

Rotating and tilting range	fixed
Angle of inclination	
Radiation direction	
Reflector / lense	asymmetrisch

**Dimensions & Weight**

Length	0,00
Width	0,00
Height	30,00
Diameter	120,00
Product Weight	326 g

**Absolute maximum ratings**

The LED will get damaged and the lifetime will decrease when you overrun absolute maximum ratings.

Working temperature	-20°C - +45°C
Storage temperature	-40°C - +60°C
IP - Code	IP54

**Article no.: 346032**

Table lamp, Head Magnetic Light Miram Black, Black, 3,7V DC, warmwhite




**General product data**

**Environmental Characteristics**

Energy label	
Energy consumption	

**Lifespan**

Lamp life time	30000 h
Luminous flux (end of lifetime)	
Number of switching cycles	15000

IP54	Protection against penetration of dust. (dust protected) Protection against penetration of splashing water.
	Lightings of Protection Class III Luminaire in which protection against electric shock relies on supply at safety extra-low voltage (SELV) and in which voltages higher than those of SELV are not generated.
	Because of the complex manufacturing process of the LED the above shown data are just a statistical size, which is not forced to be the realistic data of every LED.
	The light source of this luminaire may only be replaced by the manufacturer or by a service technician appointed by him or by a comparable qualified person