


Artikel Nr.: 341010

Wandaufbauleuchte, Relono, weiß, 220-240V AC/50-60Hz, 2x max. 40,00 W

Technische Daten

Charakteristik

Material	Gips
Farbe	weiß
Optik	überstreichbar
im Lieferumfang	



Elektrische Daten

Leistung	2x max. 40,00 W
Eingangsspannung	220-240V AC/50-60Hz
Eingangsstrom	
Fassung / Sockel	E14
Anzahl Sockel	2
Netzgerät	
Anschlussmöglichkeit	Klemme
Schutzklasse I, II, III	I

Artikel Nr.: 341010

Wandaufbauleuchte, Relono, weiß, 220-240V AC/50-60Hz, 2x max. 40,00 W

Lichtrichtung

Dreh- und Schwenkbereich	feststehend
Neigungswinkel	
Abstrahlverhalten	
Reflektor / Linse	symmetrisch



Abmessungen und Gewicht

Länge	260,00
Breite	90,00
Höhe	300,00
Durchmesser	0,00
Gewicht	2142 g

Grenzwerte

Betriebstemperatur	-5°C - +40°C
Lagertemperatur	
IP - Schutzart	IP20

EEI	Die Leuchte ist geeignet für Leuchtmittel der Energieeffizienzklassen A++ bis E
IP20	Schutz gegen das Eindringen von Fremdkörper > 50 mm. Kein Schutz gegen das Eindringen von Wasser.
	Gips ist ein Naturprodukt und unterliegt natürlichen Schwankungen in der Qualität. Verschmutzungen und Unebenheiten entfernen Sie mit dem beiliegendem Schleifpapier.
	Leuchte der Schutzklasse I bei der der Schutz gegen elektrischen Schlag nicht allein auf der Basisisolierung beruht, sondern die eine zusätzliche Sicherheitsvorkehrung derart enthält, dass berührbare leitfähige Teile mit Mitteln zum Anschluss an den Schutzleiter der festen Installation ausgerüstet sind, so dass im Fehlerfall der Basisisolierung berührbare leitfähige Teile nicht aktiv werden können.
	Aufgrund des komplexen Herstellungsprozesses von LED stellen die angegebenen Werte nur rein statistische Größen dar und müssen nicht zwingend den tatsächlichen Parametern jedes einzelnen LED-Moduls entsprechen, sondern können von den typischen Werten abweichen.


Article no.: 341010

Surface mounted wall lamp, Relono, white, 220-240V AC/50-60Hz, 2x max. 40,00 W

Technical Data

General Characteristics

Material	gypsum
Colour	white
Optics	paintable
included in delivery	



Electrical Characteristics


Power	2x max. 40,00 W
Input Voltage	220-240V AC/50-60Hz
Input current	
Base (standard designation)	E14
Number of Bases	2
Power supply unit	
Connection possibility	clamp
Protection class I, II, III	I

Article no.: 341010

Surface mounted wall lamp, Relono, white, 220-240V AC/50-60Hz, 2x max. 40,00 W

Light Direction

Rotating and tilting range	fixed
Angle of inclination	
Radiation direction	
Reflector / lense	symmetrisch



Dimensions & Weight

Length	260,00
Width	90,00
Height	300,00
Diameter	0,00
Product Weight	2142 g

Absolute maximum ratings

Working temperature	-5°C - +40°C
Storage temperature	
IP - Code	IP20

EEI	The luminaire is suitable for lamps of energy efficiency classes A++ to E.
IP20	Protection against penetration of foreign objects > 50 mm. No protection against penetration of water.
	Gypsum is a natural product and is subject to natural variations in the quality. Dirt and bumps can be removed with the included sandpaper.
	Lightings of Protection Class I in which the protection against electric shock is not based solely on isolation, but an additional safety measure contains such a way that accessible conductive parts are equipped with means for connection to the protective conductor of the fixed installation, so that in case of failure of the basic insulation exposed conductive parts cannot be active.
	Because of the complex manufacturing process of the LED the above shown data are just a statistical size, which is not forced to be the realistic data of every LED.