

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0714393464

Status:

Active

Overview:

1.00mm Mezzanine (IEEE 1386)

Description:

1.00mm Mezz (IEEE 1386) Receptacle, Surface Mount, Dual Row, Vertical Stacking, Embossed Tape on Reel, 0.76µm Gold (Au), 64 Circuits Pick and Place Cap

Documents:

3D Model

Packaging Specification PK-70873-063-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

3D Model (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Receptacles

Series

71439

Application

Board-to-Board, Signal

Overview

1.00mm Mezzanine (IEEE 1386)

Product Name

1.00mm Mezzanine (IEEE 1386)

UPC

800753784963

Physical

Circuits (Loaded)

64

Circuits (maximum)

64

Color - Resin

Natural

Flammability

94V-0

Glow-Wire Capable

No

Lock to Mating Part

Yes

Mated Height

14.00mm, 15.00mm

Material - Metal

Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

1.470/g

Number of Rows

2

Orientation

Vertical

PCB Locator

Yes

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Embossed Tape on Reel

Pitch - Mating Interface

1.00mm

Plating min - Mating

0.762µm

Plating min - Termination

1.905µm

Polarized to PCB

No

Robotic Placement

Pick and Place Cap

Surface Mount Compatible (SMC)

N/A

Temperature Range - Operating

-55° to +85°C

Termination Interface: Style

Surface Mount

Electrical

Current - Maximum per Contact

1.0A

Voltage - Maximum

100V


Solder Process Data

Duration at Max. Process Temperature (seconds)

040

Lead-freeProcess Capability

REFLOW



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

71439 Series

Mates With

71436 1.00mm Mezz (IEEE 1386) Plug. Be
sure to match like stack heights

Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-70873-063-001
Sales Drawing	714393000-000, SDA-71439-3XXX-002

This document was generated on 12/20/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION