

Artikel Nr.: 731087

Wandaufbauleuchte, Ancha I, Graphitgrau RAL 7024, 220-240V AC/50-60Hz, Warmweiß

Technische Daten

Charakteristik

Material	Aluminium Druckguss / Kunststoff
Farbe	Graphitgrau RAL 7024
Optik	/ milchig
im Lieferumfang	2x Schrauben mit Dübel 1x Innensechskantschlüssel



Elektrische Daten

Leistung	6,00 W
Eingangsspannung	220-240V AC/50-60Hz
Eingangsstrom	
Fassung / Sockel	
Anzahl Sockel	
Netzgerät	AC LED-Chip
Ansteuerung	nicht dimmbar
Anschlussmöglichkeit	Klemme
Schutzklasse I, II, III	I

Lichttechnische Eigenschaften

Leuchtmittel	Lichtquelle fest
Lichtfarbe	Warmweiß
Farbtemperatur	3000 K
Lichtstrom	260 lm
Abstrahlwinkel	113°
LED Typ	AC SMD
LED Anzahl	1
Strahlungsverteilung	582 nm




Artikel Nr.: 731087

Wandaufbauleuchte, Ancha I, Graphitgrau RAL 7024, 220-240V AC/50-60Hz, Warmweiß


Lichtrichtung

Dreh- und Schwenkbereich	feststehend
Neigungswinkel	
Abstrahlverhalten	
Reflektor / Linse	



Abmessungen und Gewicht

Länge (mm)	80,00
Breite (mm)	92,00
Höhe (mm)	97,00
Durchmesser (mm)	0,00
Deckenabhängung (mm)	0,00
Gewicht	463 g



Sockelmaß

Länge (mm)	74,00
Breite (mm)	12,00
Höhe (mm)	83,00
Durchmesser (mm)	0,00

Artikel Nr.: 731087

Wandaufbauleuchte, Ancha I, Graphitgrau RAL 7024, 220-240V AC/50-60Hz, Warmweiß

Grenzwerte

Betriebstemperatur	-5°C - +40°C
Lagertemperatur	-10°C - +60°C
IP - Schutzart	IP54

Allgemeine Eigenschaften

Umwelteigenschaften

Energieeffizienzklasse	G
Energieverbrauch	6 kWh/1000h

Lebensdauer

Lebensdauer	30000 h
Lichtstrom Ende Lebensdauer	0,70
Schaltzyklen	100000

EEI	Dieses Produkt enthält eine Lichtquelle der Energieeffizienzklasse G
IP54	Schutz gegen das Eindringen von Staub. (Staubschutz) Geschützt gegen Spritzwasser.
	Leuchte der Schutzklasse I bei der der Schutz gegen elektrischen Schlag nicht allein auf der Basisisolierung beruht, sondern die eine zusätzliche Sicherheitsvorkehrung derart enthält, dass berührbare leitfähige Teile mit Mitteln zum Anschluss an den Schutzleiter der festen Installation ausgerüstet sind, so dass im Fehlerfall der Basisisolierung berührbare leitfähige Teile nicht aktiv werden können.

Article no.: 731087

Surface mounted wall lamp, Ancha I, Graphite grey RAL 7024, 220-240V AC/50-60Hz, warmwhite

Technical Data**General Characteristics**

Material	aluminum die casting / plastic
Colour	Graphite grey RAL 7024
Optics	/ milky
included in delivery	2x screws with dowels 1x hexagon socket wrench

**Electrical Characteristics**

Power	6,00 W
Input voltage	220-240V AC/50-60Hz
Input current	
Base (standard designation)	
Number of bases	
Power supply unit	AC LED-Chip
Electronically reversible	not dimmable
Connection possibility	clamp
Protection class I, II, III	I

Light Technical Data

Bulb	Lichtquelle fest
Colour Designation	warmwhite
Colour temperature	3000 K
Luminous flux	260 lm
Beam angle	113°
LED type	AC SMD
LED quantity	1
Spectral power distribution	582 nm




Article no.: 731087


Surface mounted wall lamp, Ancha I, Graphite grey RAL 7024, 220-240V AC/50-60Hz, warmwhite

Light Direction

Rotating and tilting range	fixed
Angle of inclination	
Radiation direction	
Reflector / lense	

**Dimensions & Weight**

Length (mm)	80,00
Width (mm)	92,00
Height (mm)	97,00
Diameter (mm)	0,00
Suspensions from ceiling (mm)	0,00
Product Weight	463 g

**Base dimensions**

Length (mm)	74,00
Width (mm)	12,00
Height (mm)	83,00
Diameter (mm)	0,00

Article no.: 731087

Surface mounted wall lamp, Ancha I, Graphite grey RAL 7024, 220-240V AC/50-60Hz, warmwhite

Absolute maximum ratings

Working temperature	-5°C - +40°C
Storage temperature	-10°C - +60°C
IP - Code	IP54

General product data**Environmental Characteristics**

Energy label	G
Energy consumption	6 kWh/1000h

Lifespan

Lamp life time	30000 h
Luminous flux (end of lifetime)	0,70
Number of switching cycles	100000

EEI	This product contains a light source of energy efficiency class G
IP54	Protection against penetration of dust. (dust protected) Protection against penetration of splashing water.
	Lightings of Protection Class I in which the protection against electric shock is not based solely on isolation, but an additional safety measure contains such a way that accessible conductive parts are equipped with means for connection to the protective conductor of the fixed installation, so that in case of failure of the basic insulation exposed conductive parts cannot be active.