

ZXS15D2

Power Handling
600 Watts RMS / 1200 Watts Max.

Technical Specifications

Impedance	Zn	2 x 2 Ohms
Voice Coil Diameter	Ø	64 mm
Voice Coil Winding Height		35 mm
Max. Linear Excursion	Xmax	+/- 14 mm
Max. Mechanical Excursion	Xmax (Peak)	+/- 26 mm
Cone Area	Sd	829 cm ²
Moving Mass	Mms	284,8 g
DC Resistance	Re	2 x 2 Ohms
Resonance Frequency	Fs	26,8 Hz
Mechanical Q-Factor	Qms	3,39
Electrical Q-Factor	Qes	0,64
Total Q-Factor	Qts	0,54
Equivalent Air Volume	VAS	120,5 L
Flux Density	B/L	17,2 N/A
Efficiency 1W/1m	SPL	88 dB

Dual Voice Coil
Subwoofer 38 cm

Recommended Enclosure

Sealed Box
 Sealed Volume: 60 - 100 L

Compact

Recommended Enclosure

Ported Box
 Vented Volume: 120 L
 Port Diameter: 2 x 100 mm
 Port Area: 160 cm²
 Port Length: 30 cm
 Tuning Freq. (Fb): 30 Hz
 -3 dB Rolloff (F3): 26 Hz

Deep Tuning

Mechanical Components

- Steel Basket
- Non-pressed Paper Cone
- Foam Surround
- Injected PP Dustcap
- Single Polycot Spider
- Dual Magnet 2 x 49 oz (2.778 g)
- Magnet Size: Ø156 x 40 mm
- Aluminium Voice Coil Former

Dimensions & Weight

External Diameter: 388 mm
 Mounting Diameter: 352 mm
 Mounting Depth: 183 mm
 Shipping Weight: 9,0 kg

