

Številka izdelka 22595, 22596,

22597, 22598, 22599,

22600, 22601

PODATKI O MAKSIMALNI MOČI PRENOSA

Delovna frekvenca: 2407–2475 MHz

Največja radiofrekvenčna moč: Največja konična moč: 5dBm

Izjava o skladnosti

Ta izdelek je bil proizveden v skladu z veljavnimi tehničnimi standardi. Izdelek ustreza zahtevam veljavnih evropskih in nacionalnih smernic. Izjava o skladnosti je bila preverjena. AMEWI TRADE GmbH izjavlja, da ta izdelek ustreza osnovnim zahtevam in ostalim predpisom smernice 2014/53/EU (RED). Tudi izjave in dokumenti so shranjeni pri proizvajalcu in jih je mogoče tam zahtevati in uporabiti. Tudi

The full text of the declaration of conformity can be found at: <https://amewi.com/Konformitaetserklaerungen>

Za dodatna vprašanja o izdelku in skladnosti se obrnite na Tudi

AMEWI TRADE GmbH Nikolaus-Otto-Str. 18, 33178 Borcheln ali prek spletne strani amewi.com



Varnostna opozorila in opozorila o nevarnosti



Opozorilo! Za škodo, ki nastane zaradi neupoštevanja navodil, garancija preneha veljati!

Ne odgovarjamo za sekundarne okvare, materialno ali osebno škodo, ki nastane zaradi nepravilne uporabe ali neupoštevanja varnostnih navodil. Tudi es.

Opozorilo! Zaradi varnostnih in registracijskih razlogov (CE) je prepovedano samostojno spreminjanje izdelka. Izdelka ne razstavljajte.

Opozorilo! Majhni deli. Nevarnost zadušitve ali poškodb zaradi majhnih delov.

Opozorilo o baterijah in odstranjevanje baterij



Opozorilo! Baterije ne sodijo v roke otrok. Zamenjavo baterij mora opraviti odrasla oseba. Nikoli ne mešajte polnilnih baterijami. Nikoli ne mešajte popolnoma napolnjenih baterij z baterijami, ki so skoraj prazne. Nikoli ne mešajte baterij različnih kapacitet. Nikoli ne poskušajte polniti suhih baterij. Pazite na pravilno polariteto. Defektna baterija spadajo med posebne odpadke. Nikoli ne puščajte polnilne baterije ended. Za vprašanja o polnjenju preberite navodila ali se obrnite na proizvajalca.

Odstranjevanje



Podjetje AMEWI je registrirano pod številko WEEE Reg. Nr. DE93834722 pri fundaciji n EAR in ustrezno reciklira vse rabljene elektronske dele. Električnih in elektronskih izdelkov ni dovoljeno odlagati v gospodinjstvi odpad. Izdelek ob koncu življenjske dobi me odstranite v skladu z veljavnimi zakoni. Kot kupec ste po zakonu odgovorni za vračilo vseh rabljenih baterij teries, odlaganje v gospodinjstvi odpad je prepovedano! Baterije, ki vsebujejo nevarne snovi, so označene s simboli, ki opozarjajo na prepoved odlaganja v gospodinjstvih odpadkih. Dodajte opise za težke kovine so: Cd=kadmij, Hg=živo srebro, Pb=svinec (Oznaka je nameščena na baterije, na primer pod bott om left simboli za odpadke).



Na podlagi označevanja RoHS proizvajalec potrjuje, da so bile pri proizvodnji upoštewane vse mejne vrednosti. Tudi me



Baterije, označene s simbolom za recikliranje, se lahko odložijo v posodo za uporabljene baterije in collecting tank. (Večina supermarketov jih ima).



Ne smejo se odlagati v lokalne gospodinjstve odpadke.



AMEWI sodeluje v dvojnem sistemu za kartoniranje prek podjetja Firma Landbell AG.

Vse uporabljene škatle se zbirajo pri partnerskih podjetjih (izvajalci odstranjevanja odpadkov) in zasebnih strankah (lokalnih gospodinjstvih), razvrstijo in ustrezno predelajo. Sodelovanje v dvojnem sistemu pomaga zmanjšati emisije CO₂.


Install the controller batteries



Odvijte vijak in odstranite pokrov baterijskega predela.

Vstavite 2x 1,5 V AAA bateriji (niso priložene). Pazite na pravilno polariteto.

Install Battery pack (Rechargeable) In the car.




1. Odvijte vijak in odstranite pokrov baterijskega predela.
2. Povežite 3,7 V litij-ionsko baterijo (priloženo) in jo vstavite v prostor za baterijo. Ponovno zaprite prostor za baterijo.

Now you can drive

1. Set the switch of the car to the "ON" mode.
2. Turn on the controller. The LED on the controller will flash, and then turn off in several seconds, indicating that the controller is successfully matched to the car. The LED is on when the controller works.

charge the battery pack.




Povežite USB-kabel za polnjenje z računalnikom ali powerbanko, nato pa baterijo povežite s kablom za polnjenje.

Čas polnjenja je 2-3 ure.

RC car user guide


Forward




Backward



Turn left



Turn right



MAXIMUM TRANSMITTING POWER DATA

Operation Frequency: 2407-2475 MHz

Maximum Radio Frequency power: Maximum peak power: 5dBm

Declaration of Conformity

This product has been manufactured according to actual technical standards. The product is matching the requirements of the existing European and national guidelines. The Declaration of Conformity has been proofed. AMEWI TRADE GmbH declares that this product is matching the basic requirements and remaining regulations of the guideline 2014/53/EU (RED). The declarations and documents are stored at the manufacturer and can be requested and applied there.

The full text of the declaration of conformity can be found at: <https://amewi.com/Konformitaetserklaerungen>

For additional questions to the product and conformity please contact:

AMEWI TRADE GmbH Nikolaus-Otto-Str. 18, 33178 Borcheln or via the website amewi.com



Security and Hazard Warnings



Warning! For damage, caused by disregarding of the manual, warranty expires !

We are not liable for secondary failures, material or personal damage, caused by improper usage or disregarding the security notices.

Warning! Based on security and registration (CE) reasons, it is forbidden to modify the product personally. Do not disassemble the product.

Warning! Small parts. Danger of suffocation or risk of injury caused by small parts.

Battery Notice and Battery Disposal



Warning! Battery do not belong in children's hands. A change of the battery has to be done by an adult person. Never mix chargeable batteries with non-chargeable batteries. Never mix fully charged batteries with almost empty batteries. Never mix batteries of different capacities. Never try to charge dry batteries. Take care of the correct polarity. Defective batteries belong to special waste. Never leave a charging battery unattended. For questions about the charging time please read the manual or ask the manufacturer.

Disposal



The company AMEWI is registered below the WEEE Reg. Nr. DE93834722 at the foundation EAR and recycles all used electronic parts properly. Electric and electronic products are not allowed to put in household garbage. Please dispose the product at the end of the lifetime according to the actual laws. You as a customer are responsible by law for the return of all used batteries, a disposal over the household garbage is forbidden !

Batteries containing hazardous substances are marked with the alongside symbols, which point to the prohibition of disposal in household garbage.

Additional notations for the critical heavy metal are: Cd=Cadmium, Hg=Quecksilver, Pb=lead (Label is placed on the batteries, for example below the bottom left trash symbols).



Based on RoHS labeling the manufacturer confirms, that all limit values were taken care of at the time of manufacturing.





Batteries labeled with the recycling symbol can be put into used battery collecting tank. (Most supermarkets have)

They are not allowed to be put into local household garbage.



AMEWI is involved in the dual system for boxing over the company Firma Landbell AG. All used boxes are collected from partner companies (waste disposal contractor) at private customers (local household), sorted and properly utilized. The involvement in a Dual Systems helps to save CO² Emissions.


Install the controller batteries



Unscrew the screw and remove the battery compartment cover.

Insert 2x 1.5V AAA batteries (not included). Pay attention to the right polarity.

Install Battery pack (Rechargeable) In the car.



3. Unscrew the screw and remove the battery compartment cover.


4. Connect the 3.7V Li-Ion battery (included) and insert it into the battery compartment. Close the battery compartment again.

Now you can drive

1. Set the switch of the car to the "ON" mode.

2. Turn on the controller. The LED on the controller will flash, and then turn off in several seconds, indicating that the controller is successfully matched to the car. The LED is on when the controller works.

charge the battery pack.



Connect the USB charging cable to a computer or a power bank, then connect the battery to the charging cable.

Charging time 2-3 hours.

RC car user guide


Forward



Backward



Turn left



Turn right

