

**Artikel Nr.: 346080**

Akkuleuchte, Canis Mini, 2,3 W, 2200/3000 K, Blau, Kobaltblau RAL 5013, 3.7 V/DC, Warmweiß (WW)

**Technische Daten**

| Charakteristik  |                     |
|-----------------|---------------------|
| Material        | Aluminium           |
| Farbe           | Kobaltblau RAL 5013 |
| Optik           | Matt                |
| im Lieferumfang |                     |



**Elektrische Daten**

|                         |               |
|-------------------------|---------------|
| Leistung                | 2,3 W         |
| Eingangsspannung        | 3.7 V/DC      |
| Eingangsstrom           |               |
| Fassung / Sockel        |               |
| Anzahl Sockel           |               |
| Netzgerät               |               |
| Ansteuerung             | Touch and Dim |
| Anschlussmöglichkeit    |               |
| Schutzklasse I, II, III | III           |

**Lichttechnische Eigenschaften**

|                      |               |
|----------------------|---------------|
| Leuchtmittel         |               |
| Lichtfarbe           | Warmweiß (WW) |
| Farbtemperatur       | 3000/2200 K   |
| Lichtstrom           | 110 lm        |
| Abstrahlwinkel       |               |
| LED Typ              | SMD           |
| LED Anzahl           |               |
| Strahlungsverteilung |               |



## Artikel Nr.: 346080

Akkuleuchte, Canis Mini, 2,3 W, 2200/3000 K, Blau, Kobaltblau RAL 5013, 3.7 V/DC, Warmweiß (WW)

### Lichtrichtung

|                          |       |
|--------------------------|-------|
| Dreh- und Schwenkbereich |       |
| Neigungswinkel           |       |
| Abstrahlverhalten        | Unten |
| Reflektor / Linse        |       |

### Abmessungen und Gewicht

|             |        |
|-------------|--------|
| Länge       | 0,00   |
| Breite      | 0,00   |
| Höhe        | 208,00 |
| Durchmesser | 76,00  |
| Gewicht     | 330 g  |

### Grenzwerte

|                    |               |
|--------------------|---------------|
| Betriebstemperatur | -20 bis 40 °C |
| Lagertemperatur    | -20 bis 50 °C |
| IP - Schutzart     | IP 65         |

Artikel Nr.: 346080

Akkuleuchte, Canis Mini, 2,3 W, 2200/3000 K, Blau, Kobaltblau RAL 5013, 3.7 V/DC, Warmweiß (WW)

Allgemeine Eigenschaften

| Umwelteigenschaften    |             |
|------------------------|-------------|
| Energieeffizienzklasse |             |
| Energieverbrauch       | 3 kWh/1000h |

| Lebensdauer                   |         |
|-------------------------------|---------|
| Bemessungslebensdauer L70/B50 | 20000 h |
| Lichtstrom Ende Lebensdauer   | 0,7     |
| Schaltzyklen                  |         |

|                                                                                     |                                                                                                                                                                                                                                                                       |
|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IP 65                                                                               | Schutz gegen das Eindringen von Staub. (Staubdicht) Geschützt gegen Strahlwasser.                                                                                                                                                                                     |
|  | Leuchte der Schutzklasse III<br>Leuchte, bei der der Schutz gegen elektrischen Schlag auf der Anwendung der Schutzkleinspannung (SELV) beruht und in der Spannungen höher als SELV nicht erzeugt werden.                                                              |
|  | Aufgrund des komplexen Herstellungsprozesses von LED stellen die angegebenen Werte nur rein statistische Größen dar und müssen nicht zwingend den tatsächlichen Parametern jedes einzelnen LED-Moduls entsprechen, sondern können von den typischen Werten abweichen. |

**Article no.: 346080**

Table lamp, Cobalt blue RAL 5013, 3.7 V/DC, Warm white (WW)

**Technical Data****General Characteristics**

|                             |                      |
|-----------------------------|----------------------|
| <b>Material</b>             | Aluminium            |
| <b>Colour</b>               | Cobalt blue RAL 5013 |
| <b>Optics</b>               | Matt                 |
| <b>included in delivery</b> |                      |

**Electrical Characteristics**

|                                    |               |
|------------------------------------|---------------|
| <b>Power</b>                       | 2,3 W         |
| <b>Input Voltage</b>               | 3.7 V/DC      |
| <b>Input current</b>               |               |
| <b>Base (standard designation)</b> |               |
| <b>Number of Bases</b>             |               |
| <b>Power supply unit</b>           |               |
| <b>Electronically reversible</b>   | Touch and Dim |
| <b>Connection possibility</b>      |               |
| <b>Protection class I, II, III</b> | III           |

**Light Technical Data**

|                                    |                 |
|------------------------------------|-----------------|
| <b>Bulb</b>                        |                 |
| <b>Colour Designation</b>          | Warm white (WW) |
| <b>Colour temperature</b>          | 3000/2200 K     |
| <b>Luminous flux</b>               | 110 lm          |
| <b>Beam angle</b>                  |                 |
| <b>LED type</b>                    | SMD             |
| <b>LED quantity</b>                |                 |
| <b>Spectral power distribution</b> |                 |



## Article no.: 346080

---

Table lamp, Cobalt blue RAL 5013, 3.7 V/DC, Warm white (WW)

### Light Direction

|                            |       |
|----------------------------|-------|
| Rotating and tilting range |       |
| Angle of inclination       |       |
| Radiation direction        | Unten |
| Reflector / lense          |       |

### Dimensions & Weight

|                |        |
|----------------|--------|
| Length         | 0,00   |
| Width          | 0,00   |
| Height         | 208,00 |
| Diameter       | 76,00  |
| Product Weight | 330 g  |

### Absolute maximum ratings

|                     |               |
|---------------------|---------------|
| Working temperature | -20 bis 40 °C |
| Storage temperature | -20 bis 50 °C |
| IP - Code           | IP 65         |

**Article no.: 346080**

Table lamp, Cobalt blue RAL 5013, 3.7 V/DC, Warm white (WW)

**Environmental Characteristics**

|                    |             |
|--------------------|-------------|
| Energy label       |             |
| Energy consumption | 3 kWh/1000h |

**Lifespan**

|                                 |         |
|---------------------------------|---------|
| Rated Life Time L70 / B50       | 20000 h |
| Luminous flux (end of lifetime) | 0,7     |
| Number of switching cycles      |         |

|                                                                                     |                                                                                                                                                                                                                  |
|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IP 65                                                                               |                                                                                                                                                                                                                  |
|  | Lightings of Protection Class III<br>Luminaire in which protection against electric shock relies on supply at safety extra-low voltage (SELV) and in which voltages higher than those of SELV are not generated. |
|  | Because of the complex manufacturing process of the LED the above shown data are just a statistical size, which is not forced to be the realistic data of every LED.                                             |