

Artikel Nr.: 840393

Stripe, 2835-140-48V-2700 K-15m, IP 20

Technische Daten

Abmessungen und Gewicht

Länge	15000,00
Breite	100,00
Höhe	40,00
Gewicht	650 g
Schnittmöglichkeit (je)	100 mm

Elektrische Daten

Leistung	10 W/m
Eingangsspannung	48 V/DC
Eingangsstrom	
Anschlussmöglichkeit	offene Kabel
Schutzklasse I, II, III	III

Lichttechnische Eigenschaften

Lichtfarbe	Warmweiß (WW)
Farbtemperatur	2700 K
Lichtstrom	/m
Abstrahlwinkel	120 Grad
LED Typ	2835
LED Anzahl	2100

Grenzwerte

Die Überschreitung der Grenzwerte und Betriebsspannung führt zu einer starken Verkürzung der Lebensdauer sowie Zerstörung der LED Module.

Betriebstemperatur	-10 bis 55 °C
Lagertemperatur	-20 bis 60 °C
IP - Schutzart	IP 20
max. zu betreibende Gesamtlänge	50 m m
Mindestbiegeradius	50 mm



Artikel Nr.: 840393

Stripe, 2835-140-48V-2700 K-15m, IP 20

Allgemeine Eigenschaften

Umwelteigenschaften

Energieeffizienzklasse	F
Energieverbrauch (1m)	10 kWh/1000h

Lebensdauer

Bemessungslebensdauer L70/B50	75000 h
Lichtstrom Ende Lebensdauer	0,7
Schaltzyklen	50000

IP 20	Schutz gegen das Eindringen von Fremdkörper > 50 mm. Kein Schutz gegen das Eindringen von Wasser.
	Leuchte der Schutzklasse III Leuchte, bei der der Schutz gegen elektrischen Schlag auf der Anwendung der Schutzkleinspannung (SELV) beruht und in der Spannungen höher als SELV nicht erzeugt werden.
	Aufgrund des komplexen Herstellungsprozesses von LED stellen die angegebenen Werte nur rein statistische Größen dar und müssen nicht zwingend den tatsächlichen Parametern jedes einzelnen LED-Moduls entsprechen, sondern können von den typischen Werten abweichen.

Article no.: 840393

Flexible LED stripe, 2835-140-48V-2700 K-15m, IP 20

Technical Data**Dimensions & Weight**

Length	15000,00
Width	100,00
Height	40,00
Product weight	650 g
Cutting possibility (each)	100 mm

Electrical Characteristics

Power	10 W/m
Input voltage	48 V/DC
Input current	
Connection possibility	Open cables
Protection class I, II, III	III

Light Technical Data

Colour Designation	Warm white (WW)
Colour temperature	2700 K
Luminous Flux	/m
Beam angle	120 Grad
LED type	2835
LED quantity	2100

Absolute maximum ratings

The LED will get damaged and the lifetime will decrease when you overrun absolute maximum ratings.

Working temperature	-10 bis 55 °C
Storage temperature	-20 bis 60 °C
IP - Code	IP 20
max. total length to be operated	50 m m
Minimum bending radius	50 mm



Article no.: 840393

Flexible LED stripe, 2835-140-48V-2700 K-15m, IP 20

General product data

Environmental Characteristics

Energy Label	F
Energy consumption (1m)	10 kWh/1000h

Lifespan

Rated Life Time L70 / B50	75000 h
Luminous flux end of lifetime	0,7
Number of switching cycles	50000

IP 20 Protection against penetration of foreign objects > 50 mm. No protection against penetration of water.



Lightings of Protection Class III
Luminaire in which protection against electric shock relies on supply at safety extra-low voltage (SELV) and in which voltages higher than those of SELV are not generated.



Because of the complex manufacturing process of the LED the above shown data are just a statistical size, which is not forced to be the realistic data of every LED.