



1000 watt / 5 litres

Incl. transparent splash protection lid with refill opening (removable)

**Kneading machine
KM 3709**



Without decoration

- High-performance kneading machine with powerful 1000 watt
- Variable electronic speed control + pulse function
- 5 litres stainless steel bowl for max. 2.5–3 kg dough preparation
- Aluminium die-cast stirring hook – for light dough like short pastry dough, crumble dough or sponge mixture
- Aluminium die-cast dough hook – for heavy dough like yeast dough, bread dough or pasta dough
- Stainless steel whisk for whipping of egg white, cream, meringue and many others
- Sturdy special gear
- 35° swivelling multifunction arm
- Unlocking mechanism for multifunction arm
- Safety circuit – machine stops when lifting the arm
- Rotary switch (blue illuminated)
- Transparent splash protection lid with refill opening (removable)
- Particularly easy to operate and clean
- Secure stand due to suction feet
- Quick-action chuck for holding the tools
- 220–240 V, 50 Hz, 1000 W



Stainless steel whisk



Aluminium die-cast stirring hook



Aluminium die-cast dough hook



35° swivelling multifunction arm

Colour: Titan
 Article no.: 263 871
 Article EAN-Code: 4 006 160 638 714
 Exportpack EAN-Code: 4 006 160 884 555

PU: 1
 20"/40"/HQ container: 720 / 1535 / 1730

Colour: Red
 Article no.: 263 873
 Article EAN-Code: 4 006 160 638 738
 Exportpack EAN-Code: 4 006 160 884 579

Dimensions: (approx. W x H x D)
 Unit: 366 x 299 x 215 mm
 Box: 418 x 345 x 244 mm