

## Power Inverter 600W TE19 24V

For mobile use of various electronic devices via 24V connection



**24V  
230V**  
Power Inverter  
DC 24V to AC 230V



**USB-A**  
USB-A QC3.0  
max. 12V or max.3A



**USB-C**  
USB-C max. 12V  
or max 3A



**Overcurrent  
Protection**

**2x 230V Sockets  
with Power Switch**

**600W**  
600W continuously  
Output Power

**High & Low  
Voltage Protection**

**Automatical Turn  
Off with Alarm**

**Built-in  
Ventilation Fan**

**M**  
Modified  
sine wave

- For mobile use of electronic devices via 24V connection
- 2x USB ports with max. 3A (max. 12V or max. 3A)
- 2x 230V safety contact sockets with power switch
- Converts 24V DC battery voltage into standard 230V AC mains voltage, for connecting various electronic devices, such as Tablets, smartphones, laptops, game consoles, TV, DVD / MP3 player, camping accessories, navigation systems and much more
- Output power max. 600W (continuous) & 1200W (peak)
- Automatic safety shutdown to secure the car battery (alarm at ~20.5V & ~29.5V)
- Protection against overload & short circuit
- Overheating protection through built-in ventilation
- Fixed bracket on device for secure attachment

### Technical Specifications:

- Input voltage of the battery DC 24V (20.5V & ~29.5V)
- Output voltage per socket AC 230V / AC frequency 50Hz nominal
- Modified sine wave
- Circuit protection (DC overload): 1x35A internal fuses
- Cable length 2x 60cm
- Weight / Dimensions:  
1.2 kg / (L) 19.8 x (W) 15.9 x (H) 7.9cm

### Package Contents:

Power Inverter 600W TE19 24V, 2x 60cm connection cables, User Manual



Article-No. 4895

