



Technical Data Sheet

PolyLite™ ABS



PolyLite[™] ABS is made with a specialty bulk-polymerized ABS resin, which has significantly lower volatile content compared to traditional ABS resins. It delivers excellent printing quality with minimal odor during printing.


PHYSICAL PROPERTIES

Property	Testing Method	Typical Value
Density	ISO1183, GB/T1033	1.12 g/cm ³ at 21°C
Melt Index	220°C, 2.16kg	9-10 g/10min
Light Transmission	N/A	N/A
Flame retardancy	UL94	V2

CHEMICAL RESISTANT DATA

Property	Testing Method
Effect of weak acids	Not Resistant
Effect of strong acids	Not Resistant
Effect of weak alkalis	Resistance
Effect of strong alkalis	Resistance
Effect of organic solvent	Not Resistant
Effect of oils and grease	No data available
Effect of Sunlight	No data available

MOISTURE ABSORPTION CURVE




THERMAL PROPERTIES

Property	Testing Method	Typical Value
Glass transition	DSC, 10°C/min	101.1 °C
Melting temperature	DSC, 10°C/min	N/A
Crystallization temperature	DSC, 10°C/min	113.5 °C
Decomposition temperature	TGA, 20°C/min	>380°C
Vicat softening temperature	ISO 306 GB/T 1633	103.9 °C
Heat deflection temperature	ISO 75 1.8MPa	98.2 °C
Heat deflection temperature	ISO 75 0.45MPa	99.6 °C
Thermal conductivity	N/A	N/A
Heat shrinkage rate	N/A	N/A

HDT CURVE

PolyLite[™] ABS

0.45Mpa-1.8Mpa



TEMPERATURE / $^{\circ}C$



MECHANICAL PROPERTIES


Property	Testing Method	Typical Value
Young's modulus (X-Y)	100 F07 OD/T 1040	2174 ± 285 MPa
Young's modulus (Z)	ISO 527, GB/T 1040	1835 ± 36 MPa
Tensile strength (X-Y)	ISO 527, GB/T 1040	33.3 ± 0.8 MPa
Tensile strength (Z)		25.4 ± 0.8 MPa
Elongation at break (X-Y)	ISO 527, GB/T 1040	2.7 ± 0.4 %
Elongation at break (Z)		2.4 ± 1.2 %
Bending modulus (X-Y)	100 170 OD/T 00/1	2844 ± 411 MPa
Bending modulus (Z)	ISO 178, GB/T 9341	N/A
Bending strength (X-Y)	IOO 170 OD/T 00/1	72.8 ± 0.7 MPa
Bending strength (Z)	ISO 178, GB/T 9341	N/A
Charpy impact strength (X-Y)	100 170 OD/T 00 40	12.6 ± 1.1 kj/m ²
Charpy impact strength (Z)	ISO 179, GB/T 9343	10.5 ± 0.4 kj/m ²

HOW TO MAKE SPECIMENS

Printing temperature	255 °C
Bed temperature	100 °C
Shell	2
Top & bottom layer	4
Infill	100%
Environmental temperature	25 °C
Cooling fan	OFF


TENSILE TESTING SPECIMEN

ASTM D638 (ISO 527, GB/T 1040)




FLEXURAL TESTING SPECIMEN

ASTM D638 (ISO 527, GB/T 1040)



IMPACT TESTING SPECIMEN

ASTM D638 (ISO 179, GB/T 1043)



DISCLAIMER:

The typical values presented in this data sheet are intended for reference and comparison purposes only. They should not be used for design specifications or quality control purposes. Actual values may vary significantly with printing conditions. End- use performance of printed parts depends not only on materials, but also on part design, environmental conditions, printing conditions, etc. Product specifications are subject to change without notice. Each user is responsible for determining the safety, lawfulness, technical suitability, and disposal/ recycling practices of Polymaker materials for the intended application. Polymaker makes no warranty of any kind, unless announced separately, to the fitness for any use or application. Polymaker shall not be made liable for any damage, injury or loss induced from the use of Polymaker materials in any application.