

# ICP403029PL-02

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V  
Safety Circuit,

## Specifications

Renata Type	ICP403029
IEC Designation	ICP053131
Part Number	101028
Contact Method:	Wire AWG 30
Safety Circuit	Yes

Nominal Voltage	3.7 V
Typical Capacity	325 mAh
Minimum Capacity	310 mAh (0.2C cut off 3.0 V at 20°C)

Internal Impedance < 310 mΩ / 30% SOC

Thickness ( t )	Max 4.4 mm (after 500 cycles)
Length ( l )	Max 31 mm (after 500 cycles)
Width ( w )	Max 31 mm (after 500 cycles)
Weight	~ 7.0 g

<b>Charging Characteristic</b>	CC/CV – Constant Current / Constant Voltage
Voltage	4.2 V CV
Current Normal	0.5 C CC – 162.5 mA
Max. Charging Current	1.0 C CC – 325 mA
Temperature at Charging	0 °C .... 45 °C

<b>Discharge Characteristic</b>	
Cut off Voltage	3.0 V
Max discharge Current	2.0 C – 650 mA ( for non continues discharge ) 1.0 C – 325 mA ( for continues discharge )
Temperature during Discharge	-20 °C ... 60 °C

Cycle Life at Room Temperature > 80% of minimum capacity after 500 cycles ( 0.5 C charge, 0.5 C discharge )

Storage Temperature -20 °C ... 45 °C  
( 0 °C ... 30 °C recommended in case of storage for more than 3 months)

## Dimensions




Illustration only. For detailed drawing please contact your sales representative.

*Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative. For safety related information please consult the ASDS document related to that product or product family. The Products of Renata SA are neither designed nor authorized for use in certain areas of application of environment. For further details we refer to our webpage [www.renata.com/downloads/restriction\\_of\\_use](http://www.renata.com/downloads/restriction_of_use)*