

Walking Test EVO



Technische Daten / specifications:

Messbereich / test range:	±1050V
Auflösung / resolution:	1 Volt
Präzision / accuracy:	5% oder/or + /-5V
Eigenwiderstand / input resistance:	10 ¹⁴ Ω
Feuchte / humidity:	1 - 95%RH (Präzision: ±2%RH bis 25°C, 10%RH~90%RH)
Temperatur / temperature:	-20°C - +60°C (Präzision / accuracy: ±1°C)
Display:	LCD 128x64pixel, 68x51mm.
Stromversorgung / power supply:	6 Alkaline-Batterien / alkaline batteries LR6 1,5V
Abmessungen / dimensions:	243x130x60mm (Gerät / instrument) Ø 35x130mm (Messkopf / probe)
Gewicht / weight:	650g (Gerät / instrument) - 250g (Messkopf / probe)
Bestellnr. / order-no.:	C-9265-080