


**POWER**

Power:	120W
Lamination:	ETFE (Ethylene tetrafluoroethylene)
Cell Type:	Monocrystalline Silicon
Cell Efficiency:	Up to 23.4%
Voltage at Max Power(Vmp):	19.6V
Current at Max Power(Imp):	6.1A
Open Circuit Voltage(OCV):	24.4V
Short Circuit Current(Isc):	6.43A

**GENERAL**

Connector:	Standard MC4 Connector
Weight:	12.57lbs (5.7kg)
Dimensions (Unfolded):	21 × 65in (53.3 × 165.2cm)
Dimensions (Folded):	21 × 18.5in (53.3 × 47cm)
Operating Temperature:	14-149°F (-10-65°C)
Best Working Temperature:	77°F (25°C)
Cable Length:	118in (3m)

