

The **MULTIWELD 200M** is a compact, single-phase power source for **MIG-MAG, flux-cored wire and MMA welding processes**. Its intuitive interface integrates two digital display screens offering simple and precise setting adjustments. Equipped with a precise four-roller unwinding system, its welding quality is impeccable even when working with aluminium.

MULTI-PROCESS

■ MIG-MAG welding:

- steel wire: Ø 0.6 - 1.0 mm
- stainless steel wire: Ø 0.8 - 1.0 mm
- aluminium wire: Ø 0.8 and 1.0 mm
- flux-cored wire (reverse polarity): Ø 0.9 mm

■ MMA welding: basic and rutile electrodes (up to Ø 4 mm).

OPTIMISED MIG-MAG SETTINGS

- Manually adjust the arc dynamics.
- **Welding aid:** a table on the front of the machine helps the user to adjust the filler wire's tension and diameter according to the thickness of the material to be welded.

USER FRIENDLY

- **Easy to read display screen**, even in bright light.
- **Simple user interface** with dials and knobs suitable for gloved hands to make adjustments easier.

BUILT-IN WIRE-FEED REEL

- Compatible wire-feed reels: Ø 200 and 300 mm
- Powerful, motorised, four-roller wire-feed reel for exceptional unwinding.
- European torch connection for quick assembly and disassembly.

PREHEATING PURE CO2 GAS


- Pre-installed outlet (36 V / 4.2 A) for heating pure CO2 welding gas (heater not included).
- Compatible with US (type A) and EURO (type C/E/F) electrical sockets.

ROBUST

- Reinforced wheels combining stability and manoeuvrability.
- Support for gas cylinders up to 4 m³ (20 L).




Supplied with:



ACCESSORIES (optional)



Flux-cored wire welding kit
Ø 0,9/1,0 & 1,2 mm
072336

+  042346 (x1)



Torch kit
MB25 (250 A)
041233



Type-A roller

Steel / Stainless steel	Ø 0.6 / 0.8	042339
	Ø 0.8 / 1.0	041189
Aluminium	Ø 0.8 / 1.0	041196
Flux-cored wire	Ø 0.9 / 1.2	042346

x1

Manometer



30 l/min
 041622
 041219
 041646

50/60 Hz	A	I ₂ MMA	I ₂ MIG	Ø mm		Ø mm	Ø mm	Sterowanie elektroniczne	m/min	équipé d'origine / original equipment / originalausstattung / equipamiento de fabrica	MIG-MAG		MMA		U ₀	cm	kg	IP	Chroniony & kompatybilny generator mocy (+/-15%)	
				GAZ	NO GAZ						EN 60974-1 (40°C)	EN 60974-1 (40°C)								
230 V 1~	16	30 → 180	30 → 200	0.6 - 1.0	0.9	✓	✓	1.6 → 4		2 → 13	0.8 1.0	115 A	90 A	104 A	80 A	65	77 x 79 x 47	34.5	IP 21	9 kW