














			
-10°C ... +70°C	-5°C ... +35°C	40 mm	$\frac{10}{13} \text{ mm}$  1...2,5...4 mm ²



100 W max.	7 650 02/05/06/07/08/10
	


7 650 02  10 AX - 250 V~  	7 650 05  10 AX - 250 V~  	7 650 06  10 AX - 250 V~  
		
7 650 07  10 AX - 250 V~  	7 650 08  10 AX - 250 V~  	7 650 10  10 AX - 250 V~  
		

7 650 11

10 A - 250 V~

 $\leq 2,5 \text{ mm}^2$

13 mm




7 650 17

10 A - 250 V~

 $\leq 2,5 \text{ mm}^2$

13 mm




7 650 18

10 A - 250 V~

 $\leq 2,5 \text{ mm}^2$

13 mm




7 651 18

6 A - 250 V~

 $\leq 2,5 \text{ mm}^2$

13 mm

7 651 46 - 7 652 46
7 653 46 - 7 654 4624VAC/24VA
24VDC/1A $\leq 1,5 \text{ mm}^2$

6 mm

4 LED = 8 mA

