

**Artikel Nr.: 110018**

Deckeneinbauring, Altair eckig, Signalweiß RAL 9003, 12V AC/DC, 1x max. 35,00 W

**Technische Daten****Charakteristik**

<b>Material</b>	Aluminium Druckguss
<b>Farbe</b>	Signalweiß RAL 9003
<b>Optik</b>	
<b>im Lieferumfang</b>	inkl. Gu5.3 / MR16 Fassung

**Elektrische Daten**

<b>Leistung</b>	1x max. 35,00 W
<b>Eingangsspannung</b>	12V AC/DC
<b>Eingangsstrom</b>	
<b>Fassung / Sockel</b>	GU5.3 / MR16
<b>Anzahl Sockel</b>	1
<b>Netzgerät</b>	exkl. Trafo
<b>Ansteuerung</b>	dimmbar über optionales Leuchtmittel
<b>Anschlussmöglichkeit</b>	offene Kabel
<b>Schutzklasse I, II, III</b>	III



**Artikel Nr.: 110018**

Deckeneinbauring, Altair eckig, Signalweiß RAL 9003, 12V AC/DC, 1x max. 35,00 W

**Lichtrichtung**


Dreh- und Schwenkbereich	feststehend
Neigungswinkel	
Abstrahlverhalten	
Reflektor / Linse	

**Abmessungen und Gewicht**

Länge	85,00
Breite	85,00
Höhe	35,00
Durchmesser	0,00
Einbautiefe	0,00
Gewicht	107 g

**Ausschnittsmaß**

Länge	0,00
Breite	0,00
Durchmesser	68,00



**Artikel Nr.: 110018**

Deckeneinbauring, Altair eckig, Signalweiß RAL 9003, 12V AC/DC, 1x max. 35,00 W

**Grenzwerte**

<b>Betriebstemperatur</b>	-5°C - +40°C
<b>Lagertemperatur</b>	-10°C - +40°C
<b>IP - Schutzart</b>	IP65

**IP65** Schutz gegen das Eindringen von Staub. (Staubdicht) Geschützt gegen Strahlwasser.



Leuchte der Schutzklasse III  
Leuchte, bei der der Schutz gegen elektrischen Schlag auf der Anwendung der Schutzkleinspannung (SELV) beruht und in der Spannungen höher als SELV nicht erzeugt werden.



Aufgrund des komplexen Herstellungsprozesses von LED stellen die angegebenen Werte nur rein statistische Größen dar und müssen nicht zwingend den tatsächlichen Parametern jedes einzelnen LED-Moduls entsprechen, sondern können von den typischen Werten abweichen.

**Article no.: 110018**

Built in ceiling lamp, Altair square, Signal white RAL 9003, 12V AC/DC, 1x max. 35,00 W

**Technical Data****General Characteristics**

<b>Material</b>	aluminum die casting
<b>Colour</b>	Signal white RAL 9003
<b>Optics</b>	
<b>included in delivery</b>	inkl. Gu5.3 / MR16 lampholder

**Electrical Characteristics**

<b>Power</b>	1x max. 35,00 W
<b>input voltage</b>	12V AC/DC
<b>input current</b>	
<b>Base (standard designation)</b>	GU5.3 / MR16
<b>Number of bases</b>	1
<b>Power supply unit</b>	excl. transformer
<b>Electronically reversible</b>	dimnable via optional bulb
<b>Connection possibility</b>	wire with open ends
<b>Protection class I, II, III</b>	III



**Article no.: 110018**

Built in ceiling lamp, Altair square, Signal white RAL 9003, 12V AC/DC, 1x max. 35,00 W

**Light Direction**


Rotating and tilting range	fixed
Angle of inclination	
Radiation direction	
Reflector / lense	

**Dimensions & Weight**

Length	85,00
Width	85,00
Height	35,00
Diameter	0,00
Mounting Depth	0,00
Product Weight	107 g

**Cut-out dimensions**

Length	0,00
Width	0,00
Diameter	68,00



**Article no.: 110018**

Built in ceiling lamp, Altair square, Signal white RAL 9003, 12V AC/DC, 1x max. 35,00 W

**Absolute maximum ratings**

<b>Working temperature</b>	-5°C - +40°C
<b>Storage temperature</b>	-10°C - +40°C
<b>IP - Code</b>	IP65

**IP65** Protection against penetration of dust. (complete dust protection) Protection against penetration of water jets.



Lightings of Protection Class III  
Luminaire in which protection against electric shock relies on supply at safety extra-low voltage (SELV) and in which voltages higher than those of SELV are not generated.



Because of the complex manufacturing process of the LED the above shown data are just a statistical size, which is not forced to be the realistic data of every LED.