

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
G	14

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D3	REVISED PER ECO-12-021425	11DEC12	KH	DR





AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
26-22 AWG STRANDED	NOT LISTED	NOT LISTED

1. STAMP AMP APPROX AS SHOWN
2. 0.00254 [.000100] MIN TIN PER ASTM B-545
3. CLEANED, UNPLATED
4. 0.00254 [.000100] MIN EXT THK GOLD PL PER ASTM B-488 OVER 0.00076 [.000030] MIN NICKEL PER SAE AMS QQ-N-290.
5. COPPER PER ASTM B-152, ANNEALED
6. NOTE DELETED
7. 0.0050[.000200] MIN EXT THK NICKEL PLATE PER SAE AMS QQ-N-290.

QTY	PACKAGE TYPE	FINISH	PART NO.
1000	LOOSE PIECE	7	2-32859-4
		4	2-32859-5
		3	32859-1
		2	32859

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C[338°F]

VOLTAGE RATING: N/A

CIRCULAR MIL AREA: 0.1-0.41mm²[202-810] STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL 5

FINISH SEE TABLE

DWN	TA BRINKMAN	2-2-93
CHK	DA PATTERSON	2-2-93
APVD	JL MECKLEY	2-2-93
PRODUCT SPEC	—	
APPLICATION SPEC	—	
WEIGHT	—	

TE Connectivity

NAME TERMINAL, RING TONGUE, BUDGET —

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-32859	—

CUSTOMER DRAWING | SCALE 10:1 | SHEET 1 OF 1 | REV D3

32859