

## Artikel Nr.: 110503

Deckeneinbauring, weiß, 12V AC/DC, 1x max. 50,00 W

### Technische Daten

#### Charakteristik

|                 |      |
|-----------------|------|
| Material        | Gips |
| Farbe           | weiß |
| Optik           |      |
| im Lieferumfang |      |



#### Elektrische Daten

|                         |                                      |
|-------------------------|--------------------------------------|
| Leistung                | 1x max. 50,00 W                      |
| Eingangsspannung        | 12V AC/DC                            |
| Eingangsstrom           |                                      |
| Fassung / Sockel        | GU5.3 / MR16                         |
| Anzahl Sockel           | 1                                    |
| Netzgerät               | exkl. Trafo                          |
| Ansteuerung             | dimmbar über optionales Leuchtmittel |
| Anschlussmöglichkeit    | offene Kabel                         |
| Schutzklasse I, II, III | III                                  |

## Artikel Nr.: 110503

Deckeneinbauring, weiß, 12V AC/DC, 1x max. 50,00 W

### Lichtrichtung


|                          |             |
|--------------------------|-------------|
| Dreh- und Schwenkbereich | schwenkbar  |
| Neigungswinkel           | 45°         |
| Abstrahlverhalten        |             |
| Reflektor / Linse        | symmetrisch |

### Abmessungen und Gewicht


|             |        |
|-------------|--------|
| Länge       | 0,00   |
| Breite      | 0,00   |
| Höhe        | 60,00  |
| Durchmesser | 155,00 |
| Einbautiefe | 110,00 |
| Gewicht     | 749 g  |

### Ausschnittsmaß

|             |        |
|-------------|--------|
| Länge       | 0,00   |
| Breite      | 0,00   |
| Durchmesser | 155,00 |



60



— Ø125 —

Ø155

## Artikel Nr.: 110503

Deckeneinbauring, weiß, 12V AC/DC, 1x max. 50,00 W

### Grenzwerte

|                    |              |
|--------------------|--------------|
| Betriebstemperatur | -5°C - +40°C |
| Lagertemperatur    |              |
| IP - Schutzart     | IP20         |

|                                                                                     |                                                                                                                                                                                                                                                                       |
|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IP20                                                                                | Schutz gegen das Eindringen von Fremdkörper > 50 mm. Kein Schutz gegen das Eindringen von Wasser.                                                                                                                                                                     |
|  | Gips ist ein Naturprodukt und unterliegt natürlichen Schwankungen in der Qualität. Verschmutzungen und Unebenheiten entfernen Sie mit dem beiliegendem Schleifpapier.                                                                                                 |
|  | Leuchte der Schutzklasse III<br>Leuchte, bei der der Schutz gegen elektrischen Schlag auf der Anwendung der Schutzkleinspannung (SELV) beruht und in der Spannungen höher als SELV nicht erzeugt werden.                                                              |
|  | Aufgrund des komplexen Herstellungsprozesses von LED stellen die angegebenen Werte nur rein statistische Größen dar und müssen nicht zwingend den tatsächlichen Parametern jedes einzelnen LED-Moduls entsprechen, sondern können von den typischen Werten abweichen. |

## Article no.: 110503

Built in ceiling lamp, white, 12V AC/DC, 1x max. 50,00 W

### Technical Data

#### General Characteristics

|                      |        |
|----------------------|--------|
| Material             | gypsum |
| Colour               | white  |
| Optics               |        |
| included in delivery |        |



#### Electrical Characteristics

|                             |                            |
|-----------------------------|----------------------------|
| Power                       | 1x max. 50,00 W            |
| input voltage               | 12V AC/DC                  |
| input current               |                            |
| Base (standard designation) | GU5.3 / MR16               |
| Number of bases             | 1                          |
| Power supply unit           | excl. transformer          |
| Electronically reversible   | dimnable via optional bulb |
| Connection possibility      | wire with open ends        |
| Protection class I, II, III | III                        |

**Article no.: 110503**

Built in ceiling lamp, white, 12V AC/DC, 1x max. 50,00 W

**Light Direction**


|                            |             |
|----------------------------|-------------|
| Rotating and tilting range | swivel      |
| Angle of inclination       | 45°         |
| Radiation direction        |             |
| Reflector / lense          | symmetrisch |

**Dimensions & Weight**


|                |        |
|----------------|--------|
| Length         | 0,00   |
| Width          | 0,00   |
| Height         | 60,00  |
| Diameter       | 155,00 |
| Mounting Depth | 110,00 |
| Product Weight | 749 g  |

**Cut-out dimensions**

|          |        |
|----------|--------|
| Length   | 0,00   |
| Width    | 0,00   |
| Diameter | 155,00 |



60



— Ø125 —

— Ø155 —

**Article no.: 110503**

Built in ceiling lamp, white, 12V AC/DC, 1x max. 50,00 W

**Absolute maximum ratings**

|                     |              |
|---------------------|--------------|
| Working temperature | -5°C - +40°C |
| Storage temperature |              |
| IP - Code           | IP20         |

|                                                                                     |                                                                                                                                                                                                                  |
|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IP20                                                                                | Protection against penetration of foreign objects > 50 mm. No protection against penetration of water.                                                                                                           |
|  | Gypsum is a natural product and is subject to natural variations in the quality.<br>Dirt and bumps can be removed with the included sandpaper.                                                                   |
|  | Lightings of Protection Class III<br>Luminaire in which protection against electric shock relies on supply at safety extra-low voltage (SELV) and in which voltages higher than those of SELV are not generated. |
|  | Because of the complex manufacturing process of the LED the above shown data are just a statistical size, which is not forced to be the realistic data of every LED.                                             |