

4

3




2

1

used for:

D-SUB HD

Part-NO.	POS.	A -0.76	B $+0.25$	C	D -0.3
163A16599X	15	31.19	16.79	25.00 $+0.12$ -0.13	6.12
163A16609X	26	39.52	25.12	33.30 $+0.15$ -0.1	6.12
163A16619X	44	53.42	38.84	47.04 ± 0.13	5.99
163A16629X	62	69.70	55.30	63.50 ± 0.13	5.99



(C) (b) NOTES:


1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin Nickel
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 22
4. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

CONEC CORPORATION
BRAMPTON, ONTARIO

tolerance



scale:

2:1

material:

SEE NOTES

title:

D-SUB HD MALE
15-62pos. SOLDER CUP

dwg no:

AutoCAD 2000

DIN-A

16K1A019A

4

sh: 1/1

part no:

SEE TABLE

CONEC CORPORATION
BRAMPTON, ONTARIO

2000

date

name

drawn

03.07.

A. Mickenbecker

appd.

03.07.

E. Mickenbecker

norm

d-old

2 x c Ä3179 06.11.2008 Sonne

3 x b Ä2226 10.05.2005 Lehmen

rev. description date name

CONEC®

4

3

2

1

A

A

B

B

C

C

D

D

E

E

F

F