






PLUG CONTACT: 131□14019X

(c) SHOULD BE USED FOR
D-SUB COMBINATION
MALE CONNECTORS




SOCKET CONTACT: 132□14019X

(c) SHOULD BE USED FOR
D-SUB COMBINATION
FEMALE CONNECTORS




INSTALLATION DIMENSION



RoHS compliant

STRIPPING DIMENSIONS




NOTES:

1. INSULATOR:
PLUG CONTACT: PTFE, BLUE
SOCKET CONTACT: PTFE, WHITE
2. CONTACT: COPPER ALLOY,
PLATING CONTACT AREA:
□ = A: GOLD FLASH OVER NICKEL
□ = J: 50 µin HARD GOLD OVER NICKEL
3. SOLDER CUP ACCEPTS CABLE AWG 20
4. RETAINING RING: COPPER ALLOY, NICKEL PLATED
5. PLUG CONTACT MAY ONLY BE MOUNTED IN
D-SUB COMBINATION MALE CONNECTORS,
SOCKET CONTACT MAY ONLY BE MOUNTED IN
D-SUB COMBINATION FEMALE CONNECTORS

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm
					date	name
				drawn	07.05.2002	Parei
				appd.	07.05.2002	E. Mickenbecker
				norm		
3 x c	Ä21-007	21.01.2021	JLE	d-old		
1 x b	Ä3527	14.12.2009	Henneb.			
a	Original					
rev.	description	date	name			

CONEC®

scale:	4:1	
material:	SEE NOTES	
title:	HIGH VOLTAGE PLUG + SOCKET CONTACT solder termination straight for D-SUB COMBINATION CONNECTORS	
dwg no:	13K1A568	DIN-A4
part no:	SEE DRAWING	
		sh: 1