



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL RELEASE	12OCT2020	GK	MN

LABEL AND LINER DESIGN



PRESENTATION



All dimensions in mm [Inches]
TE PN: C63185-000

OUTSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 10000

MATERIAL	HIGH TACK MATTE METALIZED POLYESTER
ADHESIVE TYPE	PERMANENT ACRYLIC
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	± 0.3 [.012]
LABEL WIDTH:	± 0.3 [.012]
WEB WIDTH:	± 0.8 [.031]
VERTICAL REPEAT:	± 0.8 [.031]*
HORIZONTAL REPEAT:	± 0.8 [.031]*
PRINT POSITIONING:	± 0.8 [.031]*
LEFT MARGIN:	± 0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC $\pm -$
	1 PLC $\pm -$
	2 PLC $\pm -$
	3 PLC $\pm -$
	4 PLC $\pm -$
	ANGLES $\pm -$
	FINISH $\pm -$
MATERIAL	
SEE TABLE	-

DWN GOPALAKRISHNA HV CHK MIKE NUTTALL APVD MIKE NUTTALL PRODUCT SPEC TTDS-118 APPLICATION SPEC - WEIGHT 0.032g	12OCT2020 12OCT2020 12OCT2020	TE Connectivity	
NAME HMM - HIGH TACK MATTE METALIZED POLYESTER LABELS		SIZE A3	CAGE CODE C2290
DRAWING NO C-HMM-381064-10-8A		RESTRICTED TO -	REV B
CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1