

# GP Batteries

## Product Specification

Model no.: CCBV



|                       |                                                                                             |
|-----------------------|---------------------------------------------------------------------------------------------|
| Product Name          | : GP 240W C to C cable with USB-A Adaptor CCBV                                              |
| Description           | : GP Charge & Sync Cable Essentials 1.5M 2-in-1 USB-C / USB-A to USB-C 240W                 |
| Application           | : USB connection from charger to USB-C / Android / Apple devices for charging/sync function |
| Length                | : 1.50 +0.05m/- 0.02 m                                                                      |
| Cable Outer Diameter  | : 4.0 mm                                                                                    |
| Data Sync Function    | : Yes                                                                                       |
| Charging Function     | : Yes                                                                                       |
| USB-A to USB-C        | : Up to 60W (Support up to 20V, 3A)                                                         |
| USB-C to USB- C       | : Up to 240W (Support 5V, 9V, 15V, 20V, 28V, 36V and 48V; 5A)                               |
| Supported Protocols   | : PD 3.1, QC 3.0                                                                            |
| Product Dimension     | : 21 (W) x 6.4 (H) x 1,500 (L) mm                                                           |
| Weight                | : 52.7g (approx.)                                                                           |
| Cable Sheath Material | : TPE                                                                                       |
| Certification         | : CE, UKCA, RoHS                                                                            |
| Warranty Period       | : 12 months from ex-factory date                                                            |