

Artikel Nr.: 341203

Wandaufbauleuchte, Apodis 800, Roségold, 220-240V AC/50-60Hz, Warmweiß

Technische Daten

Charakteristik

Material	Aluminium
Farbe	Roségold / Schwarz
Optik	
im Lieferumfang	2x Schrauben mit Dübel 1x Innensechskantschlüssel

Elektrische Daten

Leistung	14,70 W
Eingangsspannung	220-240V AC/50-60Hz
Eingangsstrom	
Fassung / Sockel	
Anzahl Sockel	
Netzgerät	inkl. LED-Netzgerät
Ansteuerung	Phasenanschnitt oder Phasenabschnitt
Anschlussmöglichkeit	Klemme
Schutzklasse I, II, III	I

Lichttechnische Eigenschaften

Leuchtmittel	Lichtquelle fest
Lichtfarbe	Warmweiß
Farbtemperatur	3000 K
Lichtstrom	450 lm
Abstrahlwinkel	30°
LED Typ	COB
LED Anzahl	2
Strahlungsverteilung	583 nm



Artikel Nr.: 341203

Wandaufbauleuchte, Apodis 800, Roségold, 220-240V AC/50-60Hz, Warmweiß

Lichtrichtung


Dreh- und Schwenkbereich	feststehend
Neigungswinkel	
Abstrahlverhalten	2 Side
Reflektor / Linse	symmetrisch

Abmessungen und Gewicht

Länge (mm)	76,00
Breite (mm)	61,00
Höhe (mm)	800,00
Durchmesser (mm)	0,00
Deckenabhängung (mm)	0,00
Gewicht	1046 g

Sockelmaß

Länge (mm)	60,00
Breite (mm)	18,00
Höhe (mm)	100,00
Durchmesser (mm)	0,00



Artikel Nr.: 341203

Wandaufbauleuchte, Apodis 800, Roségold, 220-240V AC/50-60Hz, Warmweiß

Grenzwerte

Betriebstemperatur	-5°C - +40°C
Lagertemperatur	-10°C - +60°C
IP - Schutzart	IP20

Allgemeine Eigenschaften

Umwelteigenschaften

Energieeffizienzklasse	G
Energieverbrauch	15 kWh/1000h

Lebensdauer

Lebensdauer	25000 h
Lichtstrom Ende Lebensdauer	0,70
Schaltzyklen	100000

EEI	Dieses Produkt enthält eine Lichtquelle der Energieeffizienzklasse G
IP20	Schutz gegen das Eindringen von Fremdkörper > 50 mm. Kein Schutz gegen das Eindringen von Wasser.
	Leuchte der Schutzklasse I bei der der Schutz gegen elektrischen Schlag nicht allein auf der Basisisolierung beruht, sondern die eine zusätzliche Sicherheitsvorkehrung derart enthält, dass berührbare leitfähige Teile mit Mitteln zum Anschluss an den Schutzleiter der festen Installation ausgerüstet sind, so dass im Fehlerfall der Basisisolierung berührbare leitfähige Teile nicht aktiv werden können.

Article no.: 341203

Surface mounted wall lamp, Apodis 800, rosegold, 220-240V AC/50-60Hz, warmwhite

Technical Data**General Characteristics**

Material	aluminum
Colour	rosegold / black
Optics	
included in delivery	2x screws with dowels# 1x hexagon socket wrench

**Electrical Characteristics**

Power	14,70 W
Input voltage	220-240V AC/50-60Hz
Input current	
Base (standard designation)	
Number of bases	
Power supply unit	incl. LED-power supply unit
Electronically reversible	leading edge or trailing edge
Connection possibility	clamp
Protection class I, II, III	I

Light Technical Data

Bulb	Lichtquelle fest
Colour Designation	warmwhite
Colour temperature	3000 K
Luminous flux	450 lm
Beam angle	30°
LED type	COB
LED quantity	2
Spectral power distribution	583 nm



Article no.: 341203

Surface mounted wall lamp, Apodis 800, rosegold, 220-240V AC/50-60Hz, warmwhite

Light Direction


Rotating and tilting range	fixed
Angle of inclination	
Radiation direction	2 Side
Reflector / lense	symmetrisch

Dimensions & Weight

Length (mm)	76,00
Width (mm)	61,00
Height (mm)	800,00
Diameter (mm)	0,00
Suspensions from ceiling (mm)	0,00
Product Weight	1046 g

Base dimensions

Length (mm)	60,00
Width (mm)	18,00
Height (mm)	100,00
Diameter (mm)	0,00



Article no.: 341203

Surface mounted wall lamp, Apodis 800, rosegold, 220-240V AC/50-60Hz, warmwhite

Absolute maximum ratings

Working temperature	-5°C - +40°C
Storage temperature	-10°C - +60°C
IP - Code	IP20

General product data**Environmental Characteristics**

Energy label	G
Energy consumption	15 kWh/1000h

Lifespan

Lamp life time	25000 h
Luminous flux (end of lifetime)	0,70
Number of switching cycles	100000

EEI	This product contains a light source of energy efficiency class G
IP20	Protection against penetration of foreign objects > 50 mm. No protection against penetration of water.
	Lightings of Protection Class I in which the protection against electric shock is not based solely on isolation, but an additional safety measure contains such a way that accessible conductive parts are equipped with means for connection to the protective conductor of the fixed installation, so that in case of failure of the basic insulation exposed conductive parts cannot be active.