
THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC	DIST
A1	–

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	H-9720	21APR92	SM	CVT
	G1	REDRAWN	6JUN05	ACK	MS
	G2	REVISED PER ECO-10-00045	12JAN10	KK	AEG
	J	ECR-11-005934	28MAR11	RK	KMA



NOTE

1 OBSOLETE PARTS: OBSOLETE CIS STERMLINING PER D.RENAUD/D.SINSI

2. MAXIMUM MOUNTING TORQUE 0.6 Nm.

	DIM. "A"	DIM. "B"	FINISH	MATERIAL	PARTNUMBER
	9,2	3,0	PLAIN	ARCAP	3-828 102-3
	9,2	3,0	TINPLATED	BRASS	3-828 102-1
	17,2	11,0	PLAIN	ARCAP	2-828 102-3
	17,2	11,0	TINPLATED	BRASS	2-828 102-1
	15,9	9,7	PLAIN	ARCAP	1-828 102-3
	15,9	9,7	TINPLATED	BRASS	1-828 102-1
1 OBSOLETE	11,2	5,0	PLAIN	ARCAP	828 102-3
	11,2	5,0	TINPLATED	BRASS	828 102-1

THIS DRAWING IS UNPUBLISHED © COPYRIGHT2000 TYCO ELECTRONICS CORPORATION ALL RIGHTS RESERVED. RELEASED FOR PUBLICATION 2005

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.2
2 PLC	±0.2
3 PLC	±
4 PLC	±
ANGLES	±2°

DWN	G.ACKERMANN	06JUN2005
CHK	M.SCHAARSCHMIDT	06JUN2005
APVD	G.FELDMEIER	06JUN2005

PRODUCT SPEC: –

APPLICATION SPEC: –

WEIGHT –

MATERIAL –

FINISH –

TE Connectivity

NAME
SCREWLOCK, FEMALE HD-SERIES
BEFESTIGUNGSSCHRAUBE, BUCHSENLEISTE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A4	00779	C-828102	–

CUSTOMER DRAWING

SCALE	SHEET	OF	REV
5:1	1	1	J