

## ZST10D2

**Dual Voice Coil  
Subwoofer 25 cm**

**Power Handling**  
**300 Watts RMS / 600 Watts Max.**

### Technical Specifications

Impedance	Zn	2 x 2 Ohms
Voice Coil Diameter	Ø	50 mm
Voice Coil Winding Height		28 mm
Max. Linear Excursion	Xmax	+/- 10 mm
Max. Mechanical Excursion	Xmax (Peak)	+/- 15 mm
Cone Area	Sd	346 cm <sup>2</sup>
Moving Mass	Mms	159 g
DC Resistance	Re	2 x 1,8 Ohms
Resonance Frequency	Fs	34,6 Hz
Mechanical Q-Factor	Qms	5,05
Electrical Q-Factor	Qes	0,89
Total Q-Factor	Qts	0,75
Equivalent Air Volume	VAS	22,5 L
VC Inductance	Le	2,15 mH
Flux Density	B/L	6,2 N/A
Efficiency 1W/1m	SPL	83 dB

### Recommended Enclosure

Ported Box	
Vented Volume:	35 L
Port Diameter:	80 mm
Port Area:	50 cm <sup>2</sup>
Port Length:	22 cm
Tuning Freq. (Fb):	38 Hz
-3 dB Rolloff (F3):	30 Hz

Deep Tuning

### Recommended Enclosure

Sealed Box	
Sealed Volume:	20 - 30 L
-3 dB Rolloff (F3):	35 Hz

Recommended Box

### Mechanical Components

- Steel Basket
- Glass-Fibre Cone
- Rubber Surround
- Glass-Fibre Dustcap
- Single Nomex Spider
- Y30 Magnet 45 oz (1.276 g)
- Magnet Size: Ø145 x 20 mm
- TIL (Glass-Fibre) Voice Coil Former

### Dimensions & Weight

External Diameter:	259 mm
Mounting Diameter:	232 mm
Mounting Depth:	90 mm
Shipping Weight:	4,8 kg

