


LED Industrieleuchte
 LED industrial luminaire


INROLED_50 Ecolab Power, 1065 mm, 24V DC

Artikel-Nr.: 110210-01
EAN: 4260556624648

Bestell-Nr.:	110210-01
Modell:	INROLED_50
Bauform:	LED Rohrleuchte
Leuchtmittel:	SMD LED
Lampenleistung:	~48 W
Lampenlichtstrom:	6417 lm
Lampenlichtausbeute:	131 lm/W
Lichtverteilung:	direkt
Lichtfarbe:	Tageslichtweiß (5200 - 5700K)
Anschlusswert Leuchte:	24V DC ± 10%
Anschluss Leuchte:	M12 A-kodiert
Schutzart:	IP67/IP69K
Schutzklasse:	III
Entblendung:	opalweiß
Abstrahlwinkel:	100°
Betriebstemperatur:	-30... +50 °C
Farbwiedergabe (Ra):	> 85
Lampenlebensdauer:	> 60.000 h
Schlagfestigkeit:	IK09
Material Abdeckung:	Polycarbonat, matt, splitterfrei mit Ecolab-Beschichtung
Höhe [B] x Breite [C]:	Ø 50 mm
Länge [A]:	1065 mm
Gewicht:	1650 g
Bruttogewicht:	1950 g
Risikogruppe:	freie Gruppe
Befestigungszubehör:	Leuchtenhalter aus metalldektierbaren PP inklusive
Dimmbar:	optional über Zubehör
Kennzeichnung:	CE, ETL Listed
Gefertigt in:	Deutschland
Besonderheit:	Food+Beverage geeignet: Ecolab zertifiziert, HACCP-Zertifikat




Lampenlebensdauer in Betriebsstunden (L80/B10)



INROLED_50 Ecolab Power, 1065 mm, 24V DC

Item number: 110210-01
EAN: 4260556624648

Order number:	110210-01
Model:	INROLED_50
Type:	LED tube luminaire
Illuminant:	SMD LED
Power consumption:	~48 W
Lamp luminous flux:	6417 lm
Lamp luminous efficiency:	131 lm/W
Light distribution:	direct
Light colour:	daylight white (5200 - 5700K)
Connected load:	24V DC ± 10%
Connection (connector):	M12 connector A-type encoded
Degree of protection:	IP67/IP69K
Class of protection:	III
Glare-free	opal white
Beam angle (optics):	100°
Operating temperature:	-30... +50 °C
Colour rendering (Ra):	> 85
Lamps lifetime:	> 60,000 h
Impact-resistant:	IK09
Cover material:	polycarbonate, milky, shatterproof with Ecolab coating
Height [B] x Width [C]:	Ø 50 mm
Length [A]:	1065 mm
Weight (net):	1650 g
Gross weight:	1950 g
Risk group (DIN EN 62471):	free group
Mounting accessories:	incl. luminaire holder made of metal detectable PP
Dimmable:	via optional accessory
Marking:	CE, ETL Listed
Made in:	Germany
Feature:	Food+Beverage suitable: Ecolab certified, HACCP certificate



Lamps lifetime in operation hours (L80/B10)