




SUBMARINE®





SENSOR




|                                        | EAN           | W  | lm<br>light<br>source | lm<br>output | K    | IP | ° (°C)    | V~          | mA  | Hz    | DF   | (kg) | ▽ (°) |  |
|----------------------------------------|---------------|----|-----------------------|--------------|------|----|-----------|-------------|-----|-------|------|------|-------|--------------------------------------------------------------------------------------|
| SUBMARINE<br>SEN 60CM<br>1X8W 840 GR   | 4099854429057 | 8  | 800                   | 650          | 4000 | 65 | -20...+35 | 220-<br>240 | 55  | 50/60 | >0.5 | 0.65 | 140   | 100000                                                                               |
| SUBMARINE<br>SEN 120CM<br>1X16W 840 GR | 4099854429095 | 16 | 1800                  | 1600         | 4000 | 65 | -20...+35 | 220-<br>240 | 95  | 50/60 | >0.7 | 1.1  | 140   | 100000                                                                               |
| SUBMARINE<br>SEN 150CM<br>1X19W 840 GR | 4099854429217 | 19 | 2200                  | 1900         | 4000 | 65 | -20...+35 | 220-<br>240 | 108 | 50/60 | >0.8 | 1.34 | 140   | 100000                                                                               |



| mm                                                                               |      |    |    |
|----------------------------------------------------------------------------------|------|----|----|
|  |      |    |    |
|                                                                                  | L    | W  | H  |
| SUBMARINE SEN 60CM<br>1X8W 840 GR                                                | 651  | 66 | 75 |
| SUBMARINE SEN 120CM<br>1X16W 840 GR                                              | 1261 | 66 | 75 |
| SUBMARINE SEN 150CM<br>1X19W 840 GR                                              | 1561 | 66 | 75 |




5




|                                     | X (mm)      | Y (mm)   |
|-------------------------------------|-------------|----------|
| SUBMARINE SEN 60CM<br>1X8W 840 GR   | 254 +/- 35  | 24 +/- 2 |
| SUBMARINE SEN 120CM<br>1X16W 840 GR | 859 +/- 35  | 24 +/- 2 |
| SUBMARINE SEN 150CM<br>1X19W 840 GR | 1134 +/- 35 | 24 +/- 2 |


6



7






8



T8 (18W, 36W, 58W)  
G13 LED only

|                                     | 220-240V~ / 50/60Hz                            |
|-------------------------------------|------------------------------------------------|
| SUBMARINE SEN 60CM<br>1X8W 840 GR   | 1xST8SP-0.6 m-8W-840-EM(SubstiTUBE® STAR 0.6)  |
| SUBMARINE SEN 120CM<br>1X16W 840 GR | 1xST8SP-1.2 m-16W-840-EM(SubstiTUBE® STAR 1.2) |
| SUBMARINE SEN 150CM<br>1X19W 840 GR | 1xST8SP-1.5 m-19W-840-EM(SubstiTUBE® STAR 1.5) |



|                                  | EAN           | n | LED     | QR code | ENERGY<br>* X = |
|----------------------------------|---------------|---|---------|---------|-----------------|
| SUBMARINE SEN 60CM 1X8W 840 GR   | 4099854429057 | 1 | AC34976 |         | E               |
| SUBMARINE SEN 120CM 1X16W 840 GR | 4099854429095 | 1 | AC34980 |         | E               |
| SUBMARINE SEN 150CM 1X19W 840 GR | 4099854429217 | 1 | AC34984 |         | E               |

\* ① Dieses Produkt enthält eine Lichtquelle der Energieeffizienzklasse <X>. ② This product contains a light source of energy efficiency class <X>. ③ Ce produit contient une source lumineuse de classe d'efficacité énergétique <X>. ④ Questo prodotto contiene una sorgente luminosa di classe di efficienza energetica <X>. ⑤ Este producto contiene una fuente luminosa de la clase de eficiencia energética <X>. ⑥ Este produto contém uma fonte de luz da classe de eficiência energética <X>. ⑦ Το προϊόν αυτό περιέχει φωτεινή πηγή της τάξης ενεργειακής απόδοσης <X>. ⑧ Dit product bevat een lichtbron van energie-efficiëntieklasse <X>. ⑨ Denna produkt innehåller en ljuskälla med energieffektivitetsklass <X>. ⑩ Tämä tuote sisältää valonlähteen, jonka energiathehokkuusluokka on <X>. ⑪ Dette produktet indeholder en lyskilde med energieffektivitetsklasse <X>. ⑫ Dette produkt indeholder en lyskilde i energieffektivitetsklasse <X>. ⑬ Tento výrobek obsahuje světelný zdroj s třídou energetické účinnosti <X>. ⑭ Данный продукт содержит энергосберегающий источник света (класса <X>). ⑮ Ez a termék egy <X> energiatékonysági osztályú fényforrást tartalmaz. ⑯ Ten produkt zawiera źródło światła o klasie efektywności energetycznej <X>. ⑰ Tento výrobok obsahuje svetelný zdroj triedy energetickej účinnosti <X>. ⑱ Та изделек vsebuje svetlobni vir razreda energetske učinkovitosti <X>. ⑲ Bu ürün, enerji verimliliği sınıfında bir ışık kaynağı içerir <X>. ⑳ Ovaj proizvod sadrži izvor svjetlosti klase energetske učinkovitosti <X>. ㉑ Acest produs conține o sursă de lumină cu clasa de eficiență energetică <X>. ㉒ Тоzi продукт включва светлинен източник с клас на енергийна ефективност <X>. ㉓ Toode sisaldab energiatõhususe klassi <X> valgusallikat. ㉔ Siame gaminyje yra šviesos šaltinis, kurio energijos vartojimo efektyvumo klasė <X>. ㉕ Ši s ražojums satur gaismas avotu, kura energoefektivitātes klase ir <X>. ㉖ Ovaj proizvod sadrži izvor svetlosti klase energetske efikasnosti <X>. ㉗ Цей виріб містить джерело світла класу енергоефективності <X>. ㉘ Бұл өнімде <X> энергия тиімділігі класының жарық көзі бар.



Points de collecte sur [www.quefairedemesdechets.fr](http://www.quefairedemesdechets.fr)



LEDVANCE SASU  
CQM, 5 rue d'Altorf  
67120 Molsheim France  
[www.ledvance.com](http://www.ledvance.com)

LEDVANCE Ltd, Sterling House,  
810 Mandarin Court, Warrington,  
Cheshire, WA1 1GG, United Kingdom

G11211006  
30.01.2025